



REVISIONS						
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	✓		O	RELEASED BGM	3-85	
✓	✓		01	REVISED: ECN AB-1519 db	4-85	gpg
			A	REV PER 0600-5631-96 TT	8-98	dlm
			B	REV PER 0600-5859-96 TT	9-98	de
			C	REV PER 0600-6476-97 TT	10-98	dl
			D	REV PER 0600-6466-97 TT	10-98	de
			F	REV PER ECO-05-013297	11-05	py
			G	REV PER OH14-0208-05	1-06	py



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
		G		SEE SHEET 1	

- 1
- CAVITY IDENTIFICATION (SEE CHART) & LINES INDICATING EVERY 5th CAVITY, MARKED OR MOLDED.
- 2
- AMP, PART NO. & DATE CODE INK STAMPED (WHITE).
- 3
- HOUSING MATL - DIALLYL PHTHALATE, COLOR: BLUE.
- 4
- CONTACT MATL - BERYLLIUM COPPER OR COPPER-NICKEL-SILICONE
- 5
- CONTACT FINISH - .000030 GOLD IN CONTACT AREA OVER .000100 NICKEL, TIN-LEAD PLATING ON SOLDER TAILS.
- 6
- CONTACT FINISH - .000030 GOLD IN CONTACT AREA OVER .000100 NICKEL TIN PLATING ON SOLDER TAILS.

6	1	41	40	80	3.975	3.900	39	4.565	4.855	80	5-533603-6
6	1	36	35	70	3.475	3.400	34	4.065	4.355	70	5-533603-5
6	1	16	15	30	1.475	1.400	14	2.065	2.355	30	5-533603-1
5	OBS	1	71	70	140	6.975	6.900	69	7.565	7.855	140
	OBS	1	68	67	134	6.675	6.600	66	7.265	7.555	134
	OBS	1	66	65	130	6.475	6.400	64	7.065	7.355	130
	OBS	1	61	60	120	5.975	5.900	59	6.565	6.855	120
	OBS	1	56	55	110	5.475	5.400	54	6.065	6.355	110
	OBS	1	51	50	100	4.975	4.900	49	5.565	5.855	100
5	OBS	1	46	45	90	4.475	4.400	44	5.065	5.355	90
		1	41	40	80	3.975	3.900	39	4.565	4.855	80
		1	36	35	70	3.475	3.400	34	4.065	4.355	70
		1	31	30	60	2.975	2.900	29	3.565	3.855	60
5	OBS	1	26	25	50	2.475	2.400	24	3.065	3.355	50
		1	21	20	40	1.975	1.900	19	2.565	2.855	40
		1	16	15	30	1.475	1.400	14	2.065	2.355	30

CAVITY IDENTIFICATION	E	D	C	B	A	NO. OF POS.	PART NO
-----------------------	---	---	---	---	---	-------------	---------

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES.
TOLERANCES ON:
DECIMALS ± .005
ANGLES ± .005

MATERIAL
3 4

FINISH
5 6

CONTRACT NO

DR 3-7-85
Brendon A. Martin

CHK James P. Scholz 3-6-85

APPD James P. Scholz 3-6-85

APPD J. Scholz 3-6-85

DSGN APPD

OTHER APPD

AMP | AMP INCORPORATED
Harrisburg, Pa. 17105

NAME
RECEPT ASSY, .100 & BOX
WITH .010X.020 POSTED
CONTACT

SIZE C FSCM NO 00779 DRAWING NO 533603

SCALE 4:1 SHEET 2