

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300080328](#)
Status: **Active**
Overview: [minichange_products](#)
Description: Mini-Change® C-Size Single-Ended Cordset, STOOW Cable, Female Straight Plug, 9 Poles, Length 3.70m (10.0')

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [130008](#)
Comments C-Size (1-1/8" - 16 UN-2B)
Connector End A Mini-Change®
Connector End B Pigtail
IP Rating IP67
NEMA Rating NEMA 6
Overview [minichange_products](#)
Product Name Mini-Change®
Type Single Ended

Physical

Cable Diameter 16.26mm (.640")
Cable Length 3.70m (12.14')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Contact Brass
Material - Coupling Nut Black Epoxy Coated Zinc
Material - Plating Mating Gold over Nickel
Orientation Straight
Poles 9
Temperature Range - Operating -20°C to +105°C
Wire Size AWG 16
Wire/Cable Type STOOW

Electrical

Current - Maximum per Contact 7A
Voltage - Maximum 600V AC/DC

Material Info

Old Part Number 309000A01F100

Reference - Drawing Numbers

Sales Drawing SD-130008-004



image - Reference only

Series

EU RoHS
RoHS Compliant by Exemption
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS

Pb

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130008Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION