

5

4

3


2

1





SPECIFICATION

Mating Cycles	500
filter type	C
Capacitance	470pF±20%
Working Voltage	100V
Current Rating	7.5A
Insulation Resistance	>1GΩ


FREQUENCY (MHz)	ATTENUATION dB
5	-
10	1dB
50	10dB
100	15dB
500	35dB
1000	32dB



PCB Layout, Component side



				Dat.	Name
			Detail.	8-JUL-02	CV
			Insp.		
			Stand.		
33267	17/11/05	JMDR			
31058	8-JUL-02	CV			
Mod.	Dat.	Name			

HARTING EURL
F-95972 ParisAll Dim. in mm
Orig. Size DIN A 4D-Sub, male, straight,
15 Poles, solder pins,
tin plated shell with
dimples and holes

TB 09642227220

Sub.

Mo?Mstab/
Scale

1.5:1

Blatt/ Page

1 / 1