

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 112193

LTR.	REV.	RECORD	DATE
A			
B			
C			

MATERIAL :

INSULATOR : PBT + THERMOPLASTIC, 30% Glass
FILLED, UL 94V-0 RATED

CONTACT MATERIAL : PHOSPHOR BRONZE

ELECTRICAL CHARACTERISTICS:




CONTACT CURRENT RATING: 1AMPS

DIELECTRIC WITHSTANDING VOLTAGE: 750V AC MIN.

CONTACT RESISTANCE : 30 MILLIOHMS MAX.

INSULATION RESISTANCE : 1000 MEGAOHMS MIN.

TEMPERATURE RATING : -55°C--+105°C



A176064	64	61.28	78.74	25.93	22.86
A176048	48	50.96	58.42	17.6	15.24
A176042	42	53.34	50.8		
A176040	40	50.8	48.26		
A176032	32	40.64	38.1		
A176028	28	35.56	33.02		
A176024	24	30.48	27.94	12.7	10.16
A174024	24	30.48	27.94		
A174022	22	27.94	25.4		
A173032	32	40.64	38.1		
A173028	28	35.56	33.02		
A173024	24	30.48	27.94	9.96	7.62
A173022	22	27.94	25.4		
A173020	20	25.4	22.86		
A173018	18	22.86	20.32		
A173016	16	20.32	17.78		
A173014	14	17.78	15.24	7.62	5.08
A173008	8	10.16	7.62		
A173006	6	7.62	5.08		
PART NO	PINS	A	B	C	D

Top Willing Co., Ltd.

Top Willing Co., Ltd.			DESCRIPTION	IC SOCKET SERIES				
			3V6.01.	A170000				
AUTHORITY	SIGNATURE	DATE		TOLERANCE UNLESS OTHERWISE SPECIFIED				
DRAWN	JAY	CONCEALED		LINEAR	±0.3 ±0.2 ±0.01			
CHK.	ALEX	RECEIVED	UNIT: mm	ANGLES	±3°			
APVD.	JACKY	CONCEALED						
DWG KIND:	CUSTOMER		REV.	A 0	SCALE	1d	SHEET	1 OF 1