


REVISIONS	CATALOG NUMBER		ISSUE	PAGE	RELEASE NO.	REPLACES
A 202107	6HM7-30		3	0F		
KED						
9JAN01						
B 203581						
GLH						
23JUL01						



NOTES

- 1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF  $\phi .087$  MAX ON  $.375 \pm .002$  CENTERS FOR USE IN TEMPERATURE RANGE -85°F TO +500°F (DOWN TO -300°F IF WIRE LEADS ARE NOT FLEXED)
- 2 - HERMETICALLY SEALED (METAL-TO-METAL, GLASS-TO-METAL)
- 3 - ALL EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIALS
- 4 - WEIGHT OF SWITCH ONLY IS 0.22 OZ MAX. WEIGHT OF CONDUCTOR GROUP ONLY IS 0.20 OZ MAX PER FOOT
- 5 - DO NOT APPLY MORE THAN 1 1/2 INCH-LBS OF TORQUE WHEN TIGHTENING MOUNTING SCREWS
- 6 - ANSI Y14.5M-1982 APPLIES

CHARACTERISTICS		ELECTRICAL DATA		SCALE	2 : 1	DO NOT PRINT
		CONTACT ARRANGEMENT		UNLESS OTHERWISE SPECIFIED		
OPERATING FORCE		S P D T		ONE PLACE (.0)		
RELEASE FORCE	7 OZ MAX	LINE VOLTAGE	INDUCTIVE LOAD	THREE PLACE (.000)	.030	
DIFFERENTIAL TRAVEL	1 OZ MIN		RESISTIVE LOAD	TWO PLACE (.00)	.015	
OVERTRAVEL	.006 MAX	28 VDC	4 AMP	ANGLES	.005	
	.003 MIN	115 VAC (400 CYCLE)	2 1/2 AMP	WEIGHT		
				5		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[6HM7-30](#)