

Patch cable - NBC-R4AC1/3,0-94G/R4AC1-RD - 1421143

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Patch cable, Ethernet CAT6_A (10 Gbps), 8-position, PUR, red, cable length: 3 m

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	
GTIN	4055626254746

Technical data

Dimensions

Length of cable	3 m
-----------------	-----

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C (RJ45 connector)
	-25 °C ... 75 °C (cable)

General data

Rated current at 40°C	0.5 A
Rated voltage	48 V
Number of positions	8
Signal type/category	Ethernet CAT6 _A , 10 Gbps (500 MHz)


Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


Drawings

Patch cable - NBC-R4AC1/3,0-94G/R4AC1-RD - 1421143

Schematic diagram



Dimensional drawing



Connector pin assignment plug RJ45

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC



B.00767

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>