




© COPYRIGHT

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED	P F
S1	REVISED PER ECO-11-005294	05APR11	HMR	



SECT. A-A



SECT. B-B

① .000030 GOLD INSIDE WIRE BARREL & ON TIP OF PIN; REMAINDER OF CONTACT IS NICKEL PLATED,

② .000050 NICKEL OVER ENTIRE CONTACT WITH .000030 GOLD OVER MATING AREA.

GOLD	②	.012 PH. BRZ	60618 -6
GOLD	①	BRASS	-5
PRE-TIN		PH. BRZ	-4
PRE-TIN		.012 BRASS	60618 -1
FINISH		MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .015 ANGLES ±

CONTRACT NO

DR M. FEHER 11-26-79

CHK D. Heide 1/4/80

APPD 1-7-80

INSULATION DIA .100 MAX

WIRE RANGE 24-18 AWG.

MATERIAL SEE TABLE

FINISH SEE TABLE

TE

TE Connectivity

NAME PIN, LOOSE PIECE, COMMERCIAL MATE-N-LOK

SIZE

A

CODE IDENT NO

00779

DRAWING NO

60618

SCALE

SHEET

CUSTOMER DRAWING