

A range of high quality UK manufactured phono plugs made from machined brass with various plating options.



- Centre contact available in hollow tube.
- Ground contact with unique ‘T’ shape slot for maximum contact area.
- Internal cable clamp for secure cable connection.
- Spring strain relief.
- Colour coded ID rings for easy cable identification.
- Attractive body styling.
- Maximum cable size 5.5mm

Rating – 5A at 200 Vdc/150 Vac max.

Insulation resistance – 100M Ω at 500 Vdc

Material	
Centre contact	: Brass, silver plated
Ground contact	: Brass, nickel plated
Insulation	: Noryl SE1
Cable clamp	: Brass, silver plated
Spring	: Spring steel, nickel plated
Cap	: Brass, nickel plated

Dimensions



Deltron Part No.	Description
330-0000	NICKEL PLATED
330-0100	NICKEL PLATED (BLACK ID RING)
330-0200	NICKEL PLATED (BLUE ID RING)
330-0500	NICKEL PLATED (RED ID RING)
330-0600	NICKEL PLATED (WHITE ID RING)
330-0700	NICKEL PLATED (YELLOW ID RING)

CONVERTED FROM PS0354 ISS2 (06.12.93) IN JAN 2003

DrgnNo 330 SERIES		TITLE THROUGH GROUNDED PHONO PLUG		ALL DIMENSIONS IN MM ANGLES IN DECIMAL DEGREES	
-------------------	--	-----------------------------------	--	---	--



ISS 2

GENERAL SPECIFICATION
FOR 330 SERIES

CUSTOMER

Aprvd Date 30/01/03

Aprvd By MC

FILTER REF

BS

Scale: NTS

Sheet 1 / 1

