

SPECIFICATIONS

Material: E-SEELS -- Silicone rubber polymer type ASTM D 1418

Mounting Nut: E-SEELS: Brass, black-oxide

Temperature Range: E-SEELS: -80°F to +400°F

Pressure Range: Exceeds 15 psi internal and 1500 psi external.
(N5032B: 10 psi)



Operational Life: 50,000 actuations (minimum).

Shelf Life: Excess of 25 years.

Resistant to: Salt spray, sunlight, ozone, weather, fungus, and most acids and lubricating oils

Agency Recognition: E-SEELS and HEXSEALS are UL-listed to UL Std. 50 types 1-13, and meet CSA standards.

Installation: If a reducing adaptor is required - see page 14 of HEXSEAL catalog HEX200 for part numbers and drawing.



ITEM NUMBER	COLOR
50154 25	DARK GRAY
50154 25 17	BLACK
50154 25 B12-6	BLUE
50154 25	CLEAR
50154 25	GREEN
50154 25	ORANGE
50154 25	RED
50154 25	YELLOW
50154 50	LIGHT GREY

D	ADDED TO COLOR TABLE				05-15-08	
C	CAD COMPUTER GENERATED				7-01-04	
B	REDRAWN				9-12-74	
REV.	DESCRIPTION				DATE	
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON EACH DIMENSION.		TITLE	BOOT, TOGGLE SWITCH #(50154)		ENG. M.M.	12-7-57
					DWN. J.PALUMBO	12-7-57
					CHKD.	
MAT'L: SILICONE RUBBER PER ASTM D 1418		APM-HEXSEAL CORPORATION	SCALE	DWG. NO.	(50154)	
FINISH: GRAY			3 : 1		HEXSEAL ®	

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.
THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE WRITTEN APPROVAL OF AN OFFICER OF THE APM-HEXSEAL CORPORATION.