





PRE-PRINTED WIRE MARKER PARTS

Pre-Printed Wire Marker	
Materials Chart	206
Wire Marker Cards	207 – 212
Porta Pack Books	213 – 214
ClipSleeve Wire Markers	215

Pre-Printed Wire Markers Materials Chart

Brady's exclusive ZipStrip® release card lets you easily remove the markers you need, when you need them.







Max. Service Type	Temp. °C	Color	Finish	Use	Special Properties
Acetate Cloth					
B-12	105	White	Matt	Wire marker for varnish dip or baking cycles	Oil and heat resistant
Aluminum Foil					
B-184	130	Silver	Matt	Permanent debossed marking	Heat, oil, solvent and abrasion resistant
Overlaminated Tedlar®					
B-605	127	White	Gloss	Machine tools; hostile environments	Heat, oil, solvent and abrasion resistant
Polyester					
B-11	130	White	Gloss	Roll-form wire marking; hostile environments	Heat, oil and solvent resistant
B-702	105	White	Gloss	Vinyl coated; machine tool labeling	Oil and mild solvent resistant; high adhesion
Polyolefin					
B-319	105	White	Matt	Computer printable sleeve markers	Permanent; not heat shrinkable
B-321	105	White/Yellow	Matt	Computer printable sleeve markers	Permanent; heat shrinkable
Vinyl					
B-292	66	White	Matt	Machine tool, flat ribbon, and wire marking	Conformable, durable; oil, water and mild solvent resistant
B-708	66	White	Gloss	Indoor/outdoor cable marking	Conformable, durable; oil, water and mild solvent resistant; self laminating
Vinyl Cloth					
B-500	82	White/Yellow	Matt	All-purpose marker	Moderate heat, oil and dirt resistance; high adhesion

Tedlar® is a registered trademark of DuPont.

Wire Marker Cards

Solid Numbers, Self-Laminating Solid Numbers, Higher Numbers



Reference Explanation:




Most Brady references in this section follow the same two-part format:

The first code indicates the Brady product being referenced, the second code indicates the marker legend.

Legend	B-500 Vinyl Cloth	B-702 Vinyl Film	B-184 Aluminum Foil	B-12 Acetate Cloth	B-292 Self-Laminating Vinyl	Markers per Card	19 mm*
0	WM-0	TWM-0	AF-0	HH-0	SLF-0	36	72
1	WM-1	TWM-1	AF-1	HH-1	SLF-1	36	72
2	WM-2	TWM-2	AF-2	HH-2	SLF-2	36	72
and so on through	and so on through	and so on through	and so on through	and so on through	SLF-3		
11	WM-11	TWM-11		HH-9		36	72
12	WM-12					36	72
25	WM-25		AF-25			36	72
26	WM-26		AF-26			36	72
and so on through	and so on through		and so on through			36/card until "100", "100" and so on through to "125" is 25/card	72
125	WM-125		AF-50			25	50

*19 mm for cable diameter: 4 - 6,5 mm/38 mm for cable diameter < 12 mm


Solid Letters – Upper Case, Self-Laminating Solid Letters, Solid Letters – Lower Case



Legend	B-500 Vinyl Cloth	B-702 Vinyl Film	B-184 Aluminum	B-12 Acetate Foil	Markers per Card	19 mm
A	WM-A	TWM-A	AF-A	HH-A	36	72
B	WM-B	TWM-B	AF-B	HH-B	36	72
C	WM-C	TWM-C	AF-C	HH-C	36	72
and so on through	and so on through	and so on through	and so on through	and so on through		
Z	WM-Z	TWM-Z	AF-Z	HH-Z	36	72

Wire Marker Cards



Solid Numbers on Coloured Background



Vinyl Cloth (B-500)

Legend	Background Colours:				Markers per Card	
	Red	Yellow	Blue	Green	38 mm	19 mm
0	WM-0-RD	WM-0-YL	WM-0-BL	WM-0-GR	36	72
1	WM-1-RD	WM-1-YL	WM-1-BL	WM-1-GR	36	72
2	WM-2-RD	WM-2-YL	WM-2-BL	WM-2-GR	36	72
and so on through	and so on through	and so on through	and so on through	and so on through		
9	WM-9-RD	WM-9-YL	WM-9-BL	WM-9-GR	36	72


Consecutive Numbers, Self-Laminating Consecutive Numbers



Legend	B-500 Vinyl Cloth	B-702 Vinyl Film	B-605 Over-Laminated	B-184 Aluminum Foil	B-12 Acetate Cloth	B-292 Self-Laminating Vinyl*	Quantity Each		Markers per Card	
							38 mm	19 mm	38 mm	19 mm
1-33	WM-1-33	TWM-1-33	OLWM-1-33	AF-1-33	HH-1-33	SLF-1-33	1	2	33	66
34-66	WM-34-66	TWM-34-66		AF-34-66	HH-34-66	SLF-34-66	1	2	33	66
67-99	WM-67-99	TWM-67-99		AF-67-99		SLF-67-99	1	2	33	66
100-124	WM-100-124			AF-100-124			1	2	25	50
125-149	WM-125-149			AF-125-149			1	2	25	50
and so on through	and so on through			and so on through						
	WM-975-999			AF-200-224			1	2	25	50

*38 mm length only


Consecutive Letters



Legend	B-500 Vinyl Cloth	Markers per Card	
		38 mm	19 mm
A-Z	WM-A-Z	26	52
A-Z plus A-J	WM-A-Z, AJ	36	72

Wire Marker Cards


Consecutive Numbers on Coloured Background (Vinyl Cloth B-500)



Legend	Background Colours:							Qty. Each Markers			
	Red	Yellow	Orange	Blue	Green	Brown	Black	No. per Card		per Card	
1-33	WM-1-33RD	WM-1-33YL	WM-1-33OR	WM-1-33BL	WM-1-33GR	WM-1-33BR	WM-1-33BK	1	2	33	66
34-66	WM-34-66RD	WM-34-66YL	WM-34-66OR	WM-34-66BL	WM-34-66GR	WM-34-66BR	WM-34-66BK	1	2	33	66
67-99	WM-67-99RD	WM-67-99YL	WM-67-99OR	WM-67-99BL	WM-67-99GR	WM-67-99BR	WM-67-99BK	1	2	33	66
100-124	WM-100-124RD	WM-100-124YL	WM-100-124OR	WM-100-124BL	WM-100-124GR	WM-100-124BR	WM-100-124BK	1	2	25	50



Note: White legend on red, green, brown and black backgrounds. All other colours have black legends.

Consecutive Letters On Coloured Background (Vinyl Cloth B-500)



Legend	Background Colour	Quantity Each		Letter per Card		Markers per Card	
		Reference		38 mm	19 mm	38 mm	19 mm
A-Z	YELLOW	WM-A-Z-YL		1	2	26	52

Consecutive Numbers Repeated, Consecutive Letters Repeated




Legend	B-500 Vinyl Cloth	B-702 Vinyl Film	B-605 Over-Laminated	B-184 Aluminum Foil	Sequences per Card		Markers per Card	
					38 mm	19 mm	38 mm	19 mm
1-3	WM-1-3				12	24	36	72
1-4	WM-1-4				9	18	36	72
1-5	WM-1-5				7	14	35	70
1-6	WM-1-6				6	12	36	72
1-8	WM-1-8				4	8	32	64
1-9	WM-1-9				4	8	36	72
0-9	WM-0-9				3	6	30	60
0-10	WM-0-10				3	6	33	66
1-10	WM-1-10		OLWM-1-10		3	6	30	60
1-12	WM-1-12	TWM-1-12			3	6	36	72
1-16	WM-1-16				2	4	32	64
1-18	WM-1-18			AF-1-18	2	4	36	64
19-36	WM-19-36				2	4	36	72


Wire Marker Cards

Consecutive Paired Numbers

Use to mark both ends of wire with the same legend, fast and easy from the same dispenser card.



Self-Laminating Write-On Wire Markers




Vinyl Cloth (B-500)

Legend	Order Reference	Pairs of Markers Per Card		Markers Per Card	
		38 mm	19 mm	38 mm	19 mm
1-16	WM-1-16-DC	16	32	32	64
17-32	WM-17-32-DC	16	32	32	64

Vinyl (B-292)

Order Reference	Write-on Area (Width x Height)	Markers per Card
38 mm Long		
SLFW-250	6.35 mm x 19.05 mm	36
SLFW-344	8.74 mm x 19.05 mm	26
SLFW-500	12.70 mm x 19.05 mm	18
SLFW-750	19.05 mm x 19.05 mm	12
SLFW-100	25.40 mm x 19.05 mm	9
19 mm Long		
SLHW-250	6.35 mm x 9.53 mm	72
SLHW-500	12.54 mm x 9.53 mm	36


Solid NEMA Colours



Background Colour	B-500 Vinyl Cloth	B-702 Vinyl Film	Markers Per Card	
			38 mm	19 mm
RED	WM-COL-RD	TWM-COL-RD	36	72
YELLOW	WM-COL-YL	TWM-COL-YL	36	72
LIGHT BLUE	WM-COL-LB	TWM-COL-LB	36	72
DARK BLUE	WM-COL-DB	TWM-COL-DB	36	72
LIGHT GREEN	WM-COL-LG	TWM-COL-LG	36	72
DARK GREEN	WM-COL-DG	TWM-COL-DG	36	72
WHITE	WM-COL-WT	TWM-COL-WT	36	72
BLACK	WM-COL-BK	TWM-COL-BK	36	72
TAN	WM-COL-TN	TWM-COL-TN	36	72
BROWN	WM-COL-BR	TWM-COL-BR	36	72
ORANGE	WM-COL-OR	TWM-COL-OR	36	72
PINK	WM-COL-PK	TWM-COL-PK	36	72
GREY	WM-COL-GY	TWM-COL-GY	36	72
MAROON	WM-COL-MR	TWM-COL-MR	36	72
OLIVE	WM-COL-OL	TWM-COL-OL	36	72
PURPLE	WM-COL-PL	TWM-COL-PL	36	72

Suffix Numbers

Use to extend numbering codes or to make up other combinations of numbers or alpha-numeric codes. For example, adding suffix number 07 to 999 produces 99907.




Vinyl Cloth (B-500)

Legend	Order Reference	Markers Per Card	
		38 mm	19 mm
00	WM-00-S	36	72
01	WM-01-S	36	72
and so on through	and so on through		
09	WM-09-S	36	72
00 through to 09	WM-00-09-S	30	60


Note: Reference WM-00-09-S is a card of markers in 00 to 09 sequence with three sequences on a card.

Solid Letters and Numbers - Conduit Markers



Legend	B-500 Vinyl Cloth	Markers Per Card	
		38 mm	19 mm
A1	WM-A1	36	72
A2	WM-A2	36	72
A3	WM-A3	36	72
L1	WM-L1	36	72
L2	WM-L2	36	72
L3	WM-L3	36	72
T1	WM-T1	36	72
T2	WM-T2	36	72

Terminal Markers




Vinyl Cloth (B-500)

Legend	Order Reference	Marker Size (mm)	Markers per Card
1 through to 48	WM-1-48-TM	8.00 x 5.00	144
49 through to 96	WM-49-96-TM	8.00 x 5.00	144
A through to Z	WM-A-Z-TM	8.00 x 5.00	156

Terminal Markers have no "I" or "O".


Wire Marker Cards

Solid Symbols – Miscellaneous



Legend	B-500	B-702	Markers Per Card	
	Vinyl Cloth	Vinyl Film	38 mm	19 mm
12V	WM-12V		25	50
24V	WM-24V		25	50
220V	WM-220V		20	40
230V	WM-230V		20	40
240V	WM-240V		20	40
440V	WM-440V		20	40
+	WM-PLS	TWM-PLS	36	72
-	WM-MIN	TWM-MIN	36	72
AC	WM-AC		36	72
DC	WM-DC		36	72
⊥	WM-GRS		36	72

Solid Numbers



Vinyl (B-708)


Legend	Order Reference	Markers Per Card
0	CAB-0	18
1	CAB-1	18
2	CAB-2	18
3	CAB-3	18
4	CAB-4	18
5	CAB-5	18
6	CAB-6	18
7	CAB-7	18
8	CAB-8	18
9	CAB-9	18

Cable Markers

Standard 101.6 mm x 228.6 mm cards provide markers for cables, multi-wire circuits, even conductors and tubing in hydraulic systems. Markers may be slit for smaller diameter cable. Markers are 89 mm long; to order half markers, write 44 mm after reference.



Consecutive Numbers or Letters




Vinyl (B-708)

Legend	Order Reference	Markers Per Card
01 through 09	CAB-01-09*	18
1 through 9	CAB-1-9*	18

*Two sets of legends per card.

Solid Letters





Vinyl (B-708)

Legend	Order Reference	Markers Per Card
A	CAB-A	18
B	CAB-B	18
C	CAB-C	18
D	CAB-D	18
E	CAB-E	18
F	CAB-F	18
N	CAB-N	18

Wire Marker Cards

Miniature Wire Markers


Solid Numbers, Solid letters



Vinyl Film (B-702)

Legend	Order Reference	Markers Per Card 12.70 mm
0	TMM-0	150
1	TMM-1	150
2	TMM-2	150
3	TMM-3	150
and so on through	and so on through	
40	TMM-40	150
A	TMM-A	150
B	TMM-B	150
C	TMM-C	150
and so on through	and so on through	
Z	TMM-Z	150


Solid Nema Colours



Vinyl Film (B-702)

Background Colour	Order Reference	Markers Per Card 12.70 mm
RED	TMM-COL-RD	108
YELLOW	TMM-COL-YL	108
LIGHT BLUE	TMM-COL-LB	108
DARK BLUE	TMM-COL-DB	108
LIGHT GREEN	TMM-COL-LG	108
DARK GREEN	TMM-COL-DG	108
WHITE	TMM-COL-WT	108
BLACK	TMM-COL-BK	108
TAN	TMM-COL-TN	108
BROWN	TMM-COL-BR	108
ORANGE	TMM-COL-OR	108
PINK	TMM-COL-PK	108
GREY	TMM-COL-GY	108
MAROON	TMM-COL-MR	108
OLIVE	TMM-COL-OL	108
PURPLE	TMM-COL-PL	108

Consecutive Numbers




Vinyl Film (B-702)

Legend	Order Reference	Quantity of Each Number per Card	Markers Per Card 12.70 mm
0 through 49	TMM-0-49	3	150
50 through 99	TMM-50-99	3	150
100 through 132	TMM-100-132	3	99
133 through 165	TMM-133-165	3	99
166 through 198	TMM-166-198	3	99
199 through 231	TMM-199-231	3	99
232 through 264	TMM-232-264	3	99
265 through 297	TMM-265-297	3	99
298 through 330	TMM-298-330	3	99
331 through 363	TMM-331-363	3	99
364 through 396	TMM-364-396	3	99
397 through 429	TMM-397-429	3	99
430 through 462	TMM-430-462	3	99
463 through 495	TMM-463-495	3	99

Micro Markers

For identification of fine wire (Diameter 0.6 mm and smaller); resists continuous heat to 121°C. Only 50 micron thick. Two numbers on each marker, 250 markers on zip-strip dispenser card. Application tool included in each package of 25 cards. Marker size: 7.94 x 2.38 mm.




Vinyl Film (B-702)

Legend	Order Reference	Markers Per Card
Solid Numbers		
0	TMXM-0	250
1	TMXM-1	250
2	TMXM-2	250
and so on through	and so on through	
17	TMXM-17	250

Legend	Order Reference	Sequences on each Card
Consecutive Numbers Repeated		
0 through 49	TMXM-0-49	5
50 through 99	TMXM-50-99	5
1 through 5	TMXM-1-5	50
1 through 10	TMXM-1-10	25
1 through 25	TMXM-1-25	10

Porta Pack Books



- Ten pages per book.
- Unique comb design allows for easy refill of book.
- Slim, lightweight, pocket-sized book is easy to carry and easy to use.
- Large selections of legends available. 15 different books...over 250 different refill packs.
- Numbers...letters...special symbols...NEMA colours.
- Includes terminal marker with each wire marker.

Vinyl Cloth (B-500)

Order Reference	Legend	Markers each Legend
PWM-PK-1	0 to 9	45
PWM-PK-2	A to Z, 0 to 15, +, -, /	10
PWM-PK-3	1 to 45	10
PWM-PK-4	1, 2, 3	150
PWM-PK-5	A, B, C	150
PWM-PK-6	T1, T2, T3	150
PWM-PK-7	L1, L2, L3	150
PWM-PK-8	1 to 15 16 to 90 A to Z, +, -, /, 0	6 4 2
PWM-PK-9	1, 2, 3, A, B, C T1, T2, T3, L1, L2, L3	45 30
PWM-PK-10	10 different NEMA colours	45
PWM-PK-11	1 to 30	15
PWM-PK-12	A to Z Blank Write-On Labels + -	15 18 8 7
PWM-PK-13	+, -, AC, DC POS, NEG, GND, NEUT Spare Blank Write-On Labels	45 33 21 21
PWM-PK-14	46 to 90	10
PWM-PK-15	1 to 45 46 to 90	5 5

Write-On Self Laminating Wire and Cable Markers

- Use Brady's labelling pens or other markers to write on legend.
- Transparent part over-wraps provide snug fitting, self-laminating shield that resists oil, water and solvents.
- For applications above or below ground.



Vinyl (B-292)


Order Reference	Legend	Marker Size (mm)	Markers Per Book	Size of Write-on Area (mm)	Max Diam. (mm)
PWC-PK-1	Blank/Write-on	19.05 x 44.45	120	19.05 x 12.70	10
PWC-PK-3	Blank/Write-on	25.40 x 76.20	60	25.40 x 19.05	18
PWC-PK-6	Blank/Write-on	25.40 x 152.40	30	25.40 x 25.40	40
PWC-PK-36	Blank/Write-on	25.40 x 76.20	30	25.40 x 19.05	18
		25.40 x 152.40	15	25.40 x 25.40	40

Self Laminating Wire Markers

- Ten pages per book.
- Same as above but with printed legends.

Vinyl (B-292)

Order Reference	Legend	Markers Each Legend	Max. Diameter mm
PWS-PK-1	0 to 9	45	12
PWS-PK-2	A to Z	10	12
	0 to 15	10	
	+	10	
	-	10	
	/	10	
PWS-PK-3	1 to 45	10	12



Order Reference	Legend	Marker Size (mm)	Markers Per Book	Size of Write-on Area (mm)	Max Diam. (mm)
PWS-PK-14	Blank/Write-on	12.70 x 38.10	180	12.70 x 19.05	6

Porta Pack Books

Porta-Pack® Accessories (continued)

Labelling Pen

Brady's labelling pens use a quick drying, permanent ink. The ink is specially formulated to resist oil, solvents, abrasion and fading.



Order Reference	Ink Colour	Quantity
MP-1	Black	12 per package or
	Fine Point	single pens are available
MP-2	Black	12 per package or
	Ultra Fine Point	single pens are available
BFS-05	Black Fine Point	1
BFS-10	Black	1
	Ultra Fine Point	

Bradypack® wire markers

Dispenser

- Wire marking is simple, clean and fast...just pull tape out, tear and wrap.
- Compact size fits in your pocket or hangs from work belt.
- Unique design allows easy access to all legends during use or when refilling.
- Lifetime guarantee on Bradypack® dispenser.

Reference	Description
BPE	Empty Dispenser
BPL	Loaded Dispenser with Legends 0 through 9



Refills

Reference	Legend	Label colour	Rolls per Legend
BPR-0	0	White	10
BPR-1	1	White	10
BPR-2	2	White	10
through to BPR-9	through to 9	White	10
BPR-0-9	0-9	White	1
BPR-10-19	10-19	White	1
through to BPR-90-99	through to 90-99	White	1
BPR-A-J	A-J	White	1
BPR-I-R	I-R	White	1
BPR-Q-Z	Q-Z	White	1
BPR-L2	L2	White	10
BPR-L3	L3	White	10
BPR-CYS	~	White	10
BPR-GRS	⊥	White	10
BPR-PLS	+	White	10
BPR-MIN	-	WHITE	10

Clip Sleeve Wire Markers

Nylon

Sizes 03 to 18 are supplied on wands with 30 sleeves per wand, 10 wands to a package. Sizes larger than 18 are packed 50 individual pieces per package. (Sizes 23 and 36 may be special-ordered mounted on wands instead of bags of 50 individual sleeves. Each pack contains 10 wands of 20 sleeves (size 23) or 15 sleeves (size 36). Specify putup desired when ordering.)

Combination Packs: PREFIX SCNC Contains 10 wands, one wand each of numbers 0 to 9.

Alpha Packs Contains 13 wands, one wand each of A to M or N to Z. (e.g. SCN07-A-M).

Note: Alpha Packs are not available in 03, 05, 23, 36, 45 or 61 sizes.

Applier Wands Separate wands for applying Size 23 and Size 36 ClipSleeve™ markers are available in packages of 5 wands. Specify SCN23-AW for Size 23 and SC36-AW for Size 36.

Colour Coding Aids Users Brady ClipSleeve™ applicator wands are colour coded for easy identification of sleeve sizes.

Size 03	maroon	Size 10	red
Size 05	grey	Size 13	dark blue
Size 07	light blue	Size 15	brown
Size 09	green	Size 18	yellow



- Markers apply quickly with a special QuikWand™ applicator.
- Place the flared "shoe" end of the wand against the wire and push sleeve onto the wire.
- Split sleeve with "chevron" locking design snaps on the wire, won't slip or slide.

For Wire Sizes	SIZE 03*	SIZE 05*	SIZE 07	SIZE 09	SIZE 10	SIZE 13
Diameter mm	0.95-1.30	1.35-1.85	1.90-2.20	2.50-2.80	2.80-3.40	3.40-4.60
LEGEND	Reference	Reference	Reference	Reference	Reference	Reference
0	SCN03-0	SCN05-0	SCN07-0	SCN09-0	SCN10-0	SCN13-0
and so on through	and so on through	and so on through	and so on through	and so on through	and so on through	and so on through
9	SCN03-9	SCN05-9	SCN07-9	SCN09-9	SCN10-9	SCN13-9
0 to 9	SCNC-03	SCNC-05	SCNC-07	SCNC-09	SCNC-10	SCNC-13
A	SCN03-A	SCN05-A	SCN07-A	SCN09-A	SCN10-A	SCN13-A
and so on through	and so on through	and so on through	and so on through	and so on through	and so on through	and so on through
Z	SCN03-Z	SCN05-Z	SCN07-Z	SCN09-Z	SCN10-Z	SCN13-Z
A to M			SCN07-A-M	SCN09-A-M	SCN10-A-M	SCN13-A-M
N to Z			SCN07-N-Z	SCN09-N-Z	SCN10-N-Z	SCN13-N-Z
+	SCN03-PLUS	SCN05-PLUS	SCN07-PLUS	SCN09-PLUS	SCN10-PLUS	SCN13-PLUS
-	SCN03-MINUS	SCN05-MINUS	SCN07-MINUS	SCN09-MINUS	SCN10-MINUS	SCN13-MINUS
BLANK		SCN05-BLANK	SCN07-BLANK	SCN09-BLANK	SCN10-BLANK	SCN13-BLANK
Parts per package	300	300	300	300	300	300

For Wire Sizes	SIZE 15	SIZE 18	SIZE 23*	SIZE 36*	SIZE 45*	SIZE 61*
Diameter mm	3.90-4.50	4.60-5.90	6.00-7.60	9.20-10.50	11.50-13.00	15.50-17.00
LEGEND	Reference	Reference	Reference	Reference	Reference	Reference
0	SCN15-0	SCN18-0	SCN23-0	SCN36-0	SCN45-0	SCN61-0
and so on through	and so on through	and so on through	and so on through	and so on through	and so on through	and so on through
9	SCN15-9	SCN18-9	SCN23-9	SCN36-9	SCN45-9	SCN61-9
0 to 9	SCNC-15	SCNC-18				
A	SCN15-A	SCN18-A	SCN23-A	SCN36-A	SCN45-A	SCN61-A
and so on through	and so on through	and so on through	and so on through	and so on through	and so on through	and so on through
Z	SCN15-Z	SCN18-Z	SCN23-Z	SCN36-Z	SCN45-Z	SCN61-Z
A to M	SCN15-A-M	SCN18-A-M				
N to Z	SCN15-N-Z	SCN18-N-Z				
+	SCN15-PLUS	SCN18-PLUS	SCN23-PLUS	SCN36-PLUS	SCN45-PLUS	SCN61-PLUS
-	SCN15-MINUS	SCN18-MINUS	SCN23-MINUS	SCN36-MINUS	SCN45-MINUS	SCN61-MINUS
Blank	SCN15-BLANK	SCN18-BLANK				
Parts per package	300	300	50	50	50	50

*Consult your local BRADY representative delivery of half alphabet wands (A-M, N-Z) in sizes 03, 05, 23, 36, 45 and 61.

Notes
