

TECHNICAL DATA SHEET

GCA04

Coaxial Amplifier



KEY FEATURES

- Wide Bandwidth, Video Gain Compensation and Amplification
- Video Gain Adjustment for Each Channel
- Transmission Range: 1Km When Using RG59/BU Coaxial Cable
- Power: DC12V
- Red LED: Power On/Off
- For Connection to Video Cameras, Multiplexers, DVR etc.
- Power Supply Included

TECHNICAL DATA SHEET

TECHNICAL SPECIFICATION

Model Number	GCA04
Video Input Channel	4
Video Output Channel	4
Audio Input Channel	Not Available
Audio Output Channel	Not Available
Video Input Level	0.8 ~ 1.2V p-p 75 Ohm
Video Output Level	1V p-p (Standard) 75 Ohm
Video Bandwidth	10Hz - 10MHz
Transmission Range	1000 Metres Maximum
Power Supply	DC12V
Power Consumption	220mA
Dimensions (W x L x H)	138 x 84 x 28
Weight	240 Grams
Material	ABS Black

Features and specification are subject to change for further improvement without any notice.