






POSITION LOCK 1 2 3 - - - - - N 2 N-IN




注記 NOTES:

1. 使用材料 MATERIAL
 ウエハー: 液晶ポリマー ガラス充填 UL94V-0 (黒)
 WAFER: LIQUID CRYSTAL POLYMER (GLASS FILLED)
 UL94V-0 (COLOR: BLACK)
 ピン: 黄銅 (t=0.15)
 PIN: BRASS (t=0.15)
2. メッキ仕様 PLATING
 ピン PIN
 金メッキ 0.25マイクロメートル以上 (コンタクト部)
 GOLD 0.25MICROMETER MINIMUM (CONTACT AREA)
 金メッキ 0.4 マイクロメートル以下 (テール部)
 GOLD 0.4MICROMETER MAXIMUM (TAIL AREA)
 下地メッキ: ニッケルメッキ 1.5 マイクロメートル以上
 UNDER PLATING: NICKEL 1.5MICROMETER MINIMUM
3. (全極数/2) = 偶数の場合に適用。
 APPLY FOR (CIRCUIT/2)=EVEN.
4. 嵌合相手: 54796 シリーズ
 MATE WITH: 54796 SERIES
5. テール平坦度は、0.08以下
 TAIL COPLANARITY TO BE 0.08MAXIMUM




NONE	18.54	17.6	19.49	55622-0901	90
	16.54	15.6	17.49	55622-0801	80
6,8,10,12,23,25	12.54	11.6	13.49	55622-0601	60
6,7,8,9,10,16,17,18,19,20	10.54	9.6	11.49	55622-0501	50
2,4,6,7,8,9,10,11,12,13,14,15,17,19	8.54	7.6	9.49	55622-0401	40
ALL	6.94	6.0	7.89	55622-0321	32
LOCK POSITION	C	B	A	MATERIAL NO.	Ck+

REVISED	EC NO: J2005-3837	2005/06/23 DRW: NESUZUKI	2005/06/24 CHK: KATOJO	2005/06/30 APP: NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	MODEL DESIGN UNITS METRIC	NO. 55622-***1	THIRD ANGLE PROJECTION
						10 UNDER	±0.2	DRAWN BY SAI HARA	DATE 00/05/30	TITLE 0.4 B-TO-B PLUG ASSY WITHOUT NAIL (HGT=1.5) -LEAD FREE-			
						10 OVER 30 UNDER	±0.25	CHECKED BY TITO	DATE 02/12/17				
						30 OVER	±0.3	APPROVED BY TOYAMAGUCHI	DATE 02/12/17	MOLEX INCORPORATED			
						ANGULAR	±3 °	MATERIAL NO. SEE CHART					
REV						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



1

DETAIL "F"



DWG. NO.
SD-55622-004

F

D

V

C

B

DO NOT SCALE DRAWING

DESIGN NO. DRAWN: CH'K: APPR:	DESIGN NO. DRAWN: CH'K: APPR:	DESIGN NO. DRAWN: CH'K: APPR:	REVISED '02/12/17 DESIGN NO. J2003-1681 DRAWN: R.TAKEUCHI CH'K: T.ITO APPR: TO.YAMAGUCHI	REVISED '02/04/03 DESIGN NO. J2002-2503 DRAWN: T.KAIHO CH'K: T.ITO APPR: TO.YAMAGUCHI	DESCRIPTION REV
			F	L	


MATERIAL 材料	注記参照 SEE NOTES
FINISH 仕上	
WIRE RANGE 適用電線範囲	
INS. RANGE 被覆外径	

GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE	DESIGN UNITS ☒ mm ☐ INCH
10 UNDER 未満	±0.2	DRAWN BY & DATE S.AIHARA '00/5/30
10 OVER 30 UNDER 以上 未満	±0.25	CHECKED BY & DATE T.ITO '02/12/17
30 OVER 以上	±0.3	APPROVED BY & DATE TO.YAMAGUCHI '02/12/17
ANGLE 角度	±3°	CAD FILENAME 55622004.S02

MODEL NO. 55622-***8	TITLE: 0.4 B-To-B PLUG Assy W/O NAIL (Hgt=1.5) Embstp Pkg
MOLEX INCORPORATED	
MATERIAL NO. SEE CHART	DRAWING NO. SD-55622-004
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	

SHT 3 OF 3	REV CAD ONLY
SIZE B	

引き出し方向
PULL OUT DIRECTION



32mm幅キャリアテープ
32mm WIDTH CARRIER TAPE

無鉛
LEAD FREE

32	33.5	19.69	55622-0908	90
		17.69	55622-0808	80
キャリアテープ幅 CARRIER TAPE WIDTH	B	(A)	MATERIAL NO.	極数 Ckt

DWG. NO.
SD-55622-004

F

D

V

C

B

DO NOT SCALE DRAWING

DESIGN NO. DRAWN: CHK'G: APPR:	DESIGN NO. DRAWN: CHK'G: APPR:	DESIGN NO. DRAWN: CHK'G: APPR:	DESIGN NO. DRAWN: CHK'G: APPR:
REVISED '02/12/17 DESIGN NO. J2003-1681 DRAWN: R.TAKEUCHI CHK'G: T.ITO APPR: TO.YAMAGUCHI			
REV			




MATERIAL 材料	注記参照 SEE NOTES
FINISH 仕上げ	
WIRE RANGE 適用電線範囲	
INS. RANGE 被覆外径	

GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE
10 UNDER 未満	DESIGN UNITS ☒ mm ☐ INCH
10 OVER 30 UNDER 以上 未満	DRAWN BY & DATE S.AIHARA '00/9/25
30 OVER 以上	CHECKED BY & DATE T.ITO '02/12/17
ANGLE 角度	APPROVED BY & DATE TO.YAMAGUCHI '02/12/17
	CAD FILENAME 55622004.S03

MODEL NO. 55622-***8	TITLE: 0.4 B-To-B PLUG Assy W/O NAIL (Hgt=1.5) Embstp Pkg
MOLEX INCORPORATED	
MATERIAL NO. SEE CHART	DRAWING NO. SD-55622-004
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	

SHT 2 OF 3	REV CAD ONLY
DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY	
FORWARD ANGLE PROJECTION	
SHEET NO. 2 OF 3	
SIZE B	

引き出し方向
PULL OUT DIRECTION



24mm幅キャリアテープ
24mm WIDTH CARRIER TAPE

無鉛
LEAD FREE

24	25.5	13.69	55622-0608	60
		11.69	55622-0508	50
		9.69	55622-0408	40
		8.09	55622-0328	32
キャリアテープ幅 CARRIER TAPE WIDTH	B	(A)	MATERIAL NO.	極数 Ck+