

PoE Injector Adapter

Power over Ethernet

PART NUMBER	DESCRIPTION
POE-32001T	Power over Ethernet Injector Adapter

Specifications

Standard Compliance:

IEEE 802.3 10BASE-T Ethernet
IEEE 802.3u 100BASE-TX Fast Ethernet
IEEE802.3af Power over Ethernet

Connector:

DC Out: Power pin: 4,5(V+), 7,8(V-)

Network Cable:

10Base-T: 4-pair UTP/STP Category 3/5e/6 cable, 100-ohm EIA/TIA-568 (up to 100m)
100Base-TX: 4-pair UTP/STP Category 5e/6 cable, 100-ohm EIA/TIA-568 (up to 100m)

LED Indicator:

Per unit: Power (green)

Dimensions:

117mm x 60mm x 35mm (L x W x H)
4.6" x 2.36" x 1.38"

Operating Temperature:

0° ~ 40°C (32° ~ 104°F)

Storage Temperature:

0° ~ 70°C (32° ~ 158°F)

Operating Humidity:

90% Humidity (non-condensing)

Power Input:

100~240V, 50~60Hz, 0.25A

Power Output:

48VDC, 0.3A

EMI and Safety:

FCC Class B, CE, UL, cUL, CE/EN60950



908 Canada Court
City of Industry, CA 91748 U.S.A.
Phone: 626.964.7873 or 800.346.6668 **Fax:** 626.964.7880
www.unicomlink.com e-mail: info@unicomlink.com

©UNICOM 2007. UNICOM is a trademark of UNICOM Electric, Inc. All rights reserved.
Specifications subject to change without notice.