

Straight Blade Devices
20A, 125/250V, 3 Pole, 3 Wire Non-Grounding
Single Receptacle

HUBBELL

Features

- Classic design

Ordering Information

Description	Device Color	UPC	Catalog Number
Phenolic	Black	783585014401	HBL6810

Listings


UL Listed to UL498 File E1706
CSA Certified to C22.2 No. 42 File 280C
NEMA® WD-6 Compliant

Specifications

Body	Phenolic
Contacts	Brass
Grounding Clip	Stainless steel
Mounting Strap	Cold rolled steel
Terminal Screws	Brass
Mounting Screws	Galvanized steel

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum
Mechanical	
Cord Accomodation	.310"-.430"(7.9-11.9)
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
Environmental	
Flammability	UL 94 V-1 or better
IP Suitability	IP20
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)



Accessories

Wallplate or Weatherproof Cover 1.40" Opening

Resources

Customer Use Drawing
eCatalog

