



## Aluminum Chassis & Bottom Plates (1444 & 1434 Series)

[Home](#)
[Products](#)
[Distributors](#)
[Technical](#)
[Contact Us](#)
[Other Options](#)

Path: [Home](#) > [Enclosure Index](#) > **Aluminum Chassis**



click to enlarge

**Shipped with  
plastic skin protection**



click to enlarge

**Natural Finish  
(Shown with protective plastic  
skin removed)**

### Key Features:

- Spot welded heavy duty construction chassis.
- Natural finish as shown above - protected through manufacturing and shipping with a plastic skin cover to ensure a high quality finish.
- Optional bottom plates are punched with 4 holes – 3/16" diameter (Chassis requires drilling to install optional bottom plates).
- Hardware not provided, please order separately - Part number **1421J6** (Pkg. of 6, 6-32 Philips head screws).
- Link here to [rubber feet options](#).
- Link here to [perforated chassis covers](#).
- UPGRADE to our [Aluminum Chassis with Walnut Sides](#).

| Part Number         |                  | PDF<br>Reader<br>File                                                                       | AutoCAD<br>.dwg File<br>(zipped)                                                            | 3D<br>Solid<br>Model<br>.igs & .stp<br>files<br>(zipped)                                    | Thick<br>(Inches) | Units | Dimensions |       |        |
|---------------------|------------------|---------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|-------------------|-------|------------|-------|--------|
| Aluminum<br>Chassis | Bottom<br>Plate  |                                                                                             |                                                                                             |                                                                                             |                   |       | Width      | Depth | Height |
| <b>1444-6</b>       | <b>1434-6</b>    | <br>214K | <br>121K | <br>107K | 0.04              | inch  | 4          | 4     | 2      |
|                     |                  |                                                                                             |                                                                                             |                                                                                             |                   | mm    | 102        | 102   | 51     |
| <b>1444-45351</b>   | <b>1434-4535</b> | <br>212K | <br>121K | <br>90K  | 0.04              | inch  | 4.5        | 3.5   | 1      |
|                     |                  |                                                                                             |                                                                                             |                                                                                             |                   | mm    | 114        | 89    | 25     |
|                     |                  |                                                                                             |                                                                                             |                                                                                             |                   | inch  | 5          | 4     | 2      |

|            |          |                                                                                     |                                                                                     |                                                                                     |      |      |     |     |     |
|------------|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------|------|-----|-----|-----|
| 1444-542   | 1434-54  |     |     |     | 0.04 |      |     |     |     |
|            |          | 212K                                                                                | 117K                                                                                | 106K                                                                                |      | mm   | 127 | 102 | 51  |
| 1444-6415  | 1434-8   |    |    |    | 0.04 | inch | 6   | 4   | 1.5 |
|            |          | 210K                                                                                | 113K                                                                                | 107K                                                                                |      | mm   | 152 | 102 | 38  |
| 1444-8     | 1434-8   |    |    |    | 0.04 | inch | 6   | 4   | 2   |
|            |          | 215K                                                                                | 121K                                                                                | 107K                                                                                |      | mm   | 152 | 102 | 51  |
| 1444-643   | 1434-8   |    |    |    | 0.04 | inch | 6   | 4   | 3   |
|            |          | 204K                                                                                | 117K                                                                                | 107K                                                                                |      | mm   | 152 | 102 | 76  |
| 1444-12    | 1434-12  |    |    |    | 0.04 | inch | 7   | 5   | 2   |
|            |          | 211K                                                                                | 121K                                                                                | 108K                                                                                |      | mm   | 178 | 127 | 51  |
| 1444-753   | 1434-12  |    |    |    | 0.04 | inch | 7   | 5   | 3   |
|            |          | 206K                                                                                | 113K                                                                                | 106K                                                                                |      | mm   | 178 | 127 | 76  |
| 1444-772   | 1434-77  |    |    |    | 0.04 | inch | 7   | 7   | 2   |
|            |          | 209K                                                                                | 113K                                                                                | 107K                                                                                |      | mm   | 178 | 178 | 51  |
| 1444-9     | 1434-10  |    |    |    | 0.04 | inch | 8   | 4   | 1   |
|            |          | 208K                                                                                | 120K                                                                                | 91K                                                                                 |      | mm   | 203 | 102 | 25  |
| 1444-10    | 1434-10  |  |  |  | 0.04 | inch | 8   | 4   | 2   |
|            |          | 208K                                                                                | 121K                                                                                | 107K                                                                                |      | mm   | 203 | 102 | 51  |
| 1444-84515 | 1434-845 |  |  |  | 0.04 | inch | 8   | 4.5 | 1.5 |
|            |          | 208K                                                                                | 104K                                                                                | 107K                                                                                |      | mm   | 203 | 114 | 38  |
| 1444-862   | 1434-86  |  |  |  | 0.04 | inch | 8   | 6   | 2   |
|            |          | 209K                                                                                | 114K                                                                                | 107K                                                                                |      | mm   | 203 | 152 | 51  |
| 1444-14    | 1434-14  |  |  |  | 0.04 | inch | 9   | 5   | 2   |
|            |          | 208K                                                                                | 105K                                                                                | 108K                                                                                |      | mm   | 229 | 127 | 51  |
| 1444-972   | 1434-97  |  |  |  | 0.04 | inch | 9   | 7   | 2   |
|            |          | 207K                                                                                | 105K                                                                                | 107K                                                                                |      | mm   | 229 | 178 | 51  |
| 1444-9552  | 1434-955 |  |  |  | 0.04 | inch | 9.5 | 5   | 2   |
|            |          | 206K                                                                                | 109K                                                                                | 107K                                                                                |      | mm   | 241 | 127 | 51  |
| 1444-95525 | 1434-955 |  |  |  | 0.04 | inch | 9.5 | 5   | 2.5 |
|            |          | 206K                                                                                | 107K                                                                                | 107K                                                                                |      | mm   | 241 | 127 | 64  |
| 1444-9553  | 1434-955 |  |  |  | 0.04 | inch | 9.5 | 5   | 3   |
|            |          | 206K                                                                                | 105K                                                                                | 107K                                                                                |      | mm   | 241 | 127 | 76  |
|            |          |  |  |  |      | inch | 10  | 5   | 3   |

|            |           |                                                                                             |                                                                                             |                                                                                             |       |      |      |     |     |
|------------|-----------|---------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|-------|------|------|-----|-----|
| 1444-1053  | 1434-105  | 205K                                                                                        | 105K                                                                                        | 108K                                                                                        | 0.04  | mm   | 254  | 127 | 76  |
| 1444-15    | 1434-16   | <br>204K   | <br>115K   | <br>91K    | 0.04  | inch | 10   | 6   | 1   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 254  | 152 | 25  |
| 1444-16    | 1434-16   | <br>203K   | <br>104K   | <br>108K   | 0.04  | inch | 10   | 6   | 2   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 254  | 152 | 51  |
| 1444-10825 | 1434-108  | <br>205K   | <br>107K   | <br>108K   | 0.04  | inch | 10   | 8   | 2.5 |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 254  | 203 | 64  |
| 1444-1172  | 1434-117  | <br>204K   | <br>104K   | <br>107K   | 0.04  | inch | 11   | 7   | 2   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 279  | 178 | 51  |
| 1444-1273  | 1434-127  | <br>203K   | <br>104K   | <br>107K   | 0.04  | inch | 12   | 7   | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 305  | 178 | 76  |
| 1444-22    | 1434-22   | <br>204K   | <br>105K   | <br>108K   | 0.051 | inch | 12   | 8   | 2   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 305  | 203 | 51  |
| 1444-12825 | 1434-22   | <br>203K   | <br>107K   | <br>109K   | 0.051 | inch | 12   | 8   | 2.5 |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 305  | 203 | 64  |
| 1444-24    | 1434-22   | <br>204K | <br>109K | <br>110K | 0.051 | inch | 12   | 8   | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 305  | 203 | 76  |
| 1444-29    | 1434-29   | <br>204K | <br>115K | <br>108K | 0.051 | inch | 12   | 10  | 2   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 305  | 254 | 51  |
| 1444-12103 | 1434-29   | <br>204K | <br>106K | <br>109K | 0.051 | inch | 12   | 10  | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 305  | 254 | 76  |
| 1444-12123 | 1434-1212 | <br>203K | <br>105K | <br>109K | 0.051 | inch | 12   | 12  | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 305  | 305 | 76  |
| 1444-1372  | 1434-137  | <br>203K | <br>106K | <br>107K | 0.04  | inch | 13   | 7   | 2   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 330  | 178 | 51  |
| 1444-18    | 1434-18   | <br>201K | <br>114K | <br>108K | 0.04  | inch | 13.5 | 5   | 2   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 343  | 127 | 51  |
| 1444-1463  | 1434-146  | <br>202K | <br>106K | <br>109K | 0.051 | inch | 14   | 6   | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 356  | 152 | 76  |
| 1444-14103 | 1434-1410 | <br>202K | <br>105K | <br>109K | 0.051 | inch | 14   | 10  | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 356  | 254 | 76  |
| 1444-1573  | 1434-157  | <br>     | <br>     | <br>     | 0.051 | inch | 15   | 7   | 3   |

|            |           |                                                                                             |                                                                                             |                                                                                             |       |      |     |     |     |
|------------|-----------|---------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|-------|------|-----|-----|-----|
|            |           | 203K                                                                                        | 105K                                                                                        | 109K                                                                                        |       | mm   | 381 | 178 | 76  |
| 1444-1593  | 1434-159  | <br>202K   | <br>106K   | <br>109K   | 0.051 | inch | 15  | 9   | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 381 | 229 | 76  |
| 1444-26    | 1434-26   | <br>200K   | <br>105K   | <br>109K   | 0.051 | inch | 16  | 8   | 2   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 406 | 203 | 51  |
| 1444-28    | 1434-26   | <br>201K   | <br>105K   | <br>110K   | 0.051 | inch | 16  | 8   | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 406 | 203 | 76  |
| 1444-20    | 1434-20   | <br>197K   | <br>105K   | <br>108K   | 0.04  | inch | 17  | 4   | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 102 | 76  |
| 1444-1763  | 1434-176  | <br>200K   | <br>107K   | <br>109K   | 0.051 | inch | 17  | 6   | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 152 | 76  |
| 1444-1773  | 1434-177  | <br>201K   | <br>106K   | <br>109K   | 0.051 | inch | 17  | 7   | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 178 | 76  |
| 1444-1783  | 1434-178  | <br>202K   | <br>107K   | <br>109K   | 0.051 | inch | 17  | 8   | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 203 | 76  |
| 1444-30    | 1434-30   | <br>199K | <br>106K | <br>109K | 0.051 | inch | 17  | 10  | 2   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 254 | 51  |
| 1444-32    | 1434-30   | <br>200K | <br>106K | <br>109K | 0.051 | inch | 17  | 10  | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 254 | 76  |
| 1444-33    | 1434-30   | <br>200K | <br>106K | <br>109K | 0.051 | inch | 17  | 10  | 4   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 254 | 102 |
| 1444-17105 | 1434-30   | <br>200K | <br>105K | <br>108K | 0.051 | inch | 17  | 10  | 5   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 254 | 127 |
| 1444-17123 | 1434-1712 | <br>200K | <br>105K | <br>109K | 0.051 | inch | 17  | 12  | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 305 | 76  |
| 1444-17132 | 1434-1713 | <br>201K | <br>106K | <br>109K | 0.051 | inch | 17  | 13  | 2   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 330 | 51  |
| 1444-17133 | 1434-1713 | <br>201K | <br>105K | <br>109K | 0.051 | inch | 17  | 13  | 3   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 330 | 76  |
| 1444-17134 | 1434-1713 | <br>200K | <br>105K | <br>109K | 0.051 | inch | 17  | 13  | 4   |
|            |           |                                                                                             |                                                                                             |                                                                                             |       | mm   | 432 | 330 | 102 |
| 1444-17135 | 1434-1713 |          |          |          | 0.051 | inch | 17  | 13  | 5   |

|            |           |                                                                                        |                                                                                        |                                                                                        |       |      |     |     |     |
|------------|-----------|----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|-------|------|-----|-----|-----|
|            |           | 200K                                                                                   | 105K                                                                                   | 109K                                                                                   |       | mm   | 432 | 330 | 127 |
| 1444-17143 | 1434-1714 |  201K |  106K |  109K | 0.051 | inch | 17  | 14  | 3   |
|            |           |                                                                                        |                                                                                        |                                                                                        |       | mm   | 432 | 356 | 76  |
| 1444-17154 | 1434-1715 |  201K |  105K |  109K | 0.051 | inch | 17  | 15  | 4   |
|            |           |                                                                                        |                                                                                        |                                                                                        |       | mm   | 432 | 381 | 102 |
| 1444-17156 | 1434-1715 |  201K |  105K |  109K | 0.051 | inch | 17  | 15  | 6   |
|            |           |                                                                                        |                                                                                        |                                                                                        |       | mm   | 432 | 381 | 152 |
| 1444-17173 | 1434-1717 |  200K |  104K |  109K | 0.051 | inch | 17  | 17  | 3   |
|            |           |                                                                                        |                                                                                        |                                                                                        |       | mm   | 432 | 432 | 76  |
| 1444-17174 | 1434-1717 |  200K |  104K |  109K | 0.051 | inch | 17  | 17  | 4   |
|            |           |                                                                                        |                                                                                        |                                                                                        |       | mm   | 432 | 432 | 102 |

## Views:

| Upside Down (to show interior)                                                                             | Optional Bottom Plate                                                                                       |
|------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------|
|  <p>click to enlarge</p> |  <p>click to enlarge</p> |
| <p><b>UPGRADE</b> to our <a href="#">Aluminum Chassis with Walnut Sides</a></p>                            |                                                                                                             |
|  <p>link here</p>      |                                                                                                             |



**NOW**

catalog pages on this series (98K) [9C-1444.pdf](#)

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!



**Our Distributors**

[Order from your favorite distributor](#)

---

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)

---

Copyright; © 1997-2013 Hammond Mfg Co Inc

URL: <http://www.hammondmfg.com>