



## Jet-Light ELH 38 spotlight

For use indoors and outdoors.

- Ideal for home improvement, repair work or camping.
- Electronic ballast for energy efficiency, flicker-free light and minimum heat output.
- Very bright light.
- Robust, break- and shock-resistant plastic housing. Cover made from break resistant polycarbonate.
- With foldable stand.
- Compact construction.
- With special rubber cable.
- 8 W bulb included.
- Ballast efficiency: A3
- Luminous flux: 2500 lm



| Article No.          | EAN-Code 4007123... | UP | Cable length | Cable         | Lamp efficacy | Colour temperature | Output | Fittings | Voltage |  |
|----------------------|---------------------|----|--------------|---------------|---------------|--------------------|--------|----------|---------|--|
| <b>1 17270 3</b>     | 592616              | 1  | 1,8 m        | H05RN-F 3G1,0 | 66 lm/W       | 6400 K             | 38 W   | GR10q    | 240 V   |  |
| <b>1 17270 3 110</b> | 610136              | 1  | 1,8 m        | H05RN-F 3G1,0 | 66 lm/W       | 6400 K             | 38 W   | GR10q    | 110 V   |  |

### Recommended accessories:

| Article No.      | EAN-Code 4007123... | UP | Description    | Output | Luminous flux | Lamp efficacy | Colour temperature | Colour rendering index | Fittings | Mercury content | Energy efficiency class |
|------------------|---------------------|----|----------------|--------|---------------|---------------|--------------------|------------------------|----------|-----------------|-------------------------|
| <b>1 17764 0</b> | 210190              | 1  | Jet-Light bulb | 38 W   | 2700 lm       | 71 lm/W       | 4200 K             | 80                     | GR10q    | 4 mg            | B                       |
| <b>1 17470 0</b> | 576265              | 1  | Jet-Light bulb | 38 W   | 2500 lm       | 66 lm/W       | 6400 K             | 80                     | GR10q    | 3,5 mg          | B                       |



## Jet-Light ELH 21 spotlight

For use indoors and outdoors.

- Ideal for home improvement, repair work or camping.
- Electronic ballast for energy efficiency, flicker-free light and minimum heat output.
- Very bright light.
- Robust, break- and shock-resistant plastic housing. Cover made from break resistant polycarbonate.
- With foldable stand.
- Compact construction.
- With special rubber cable.
- 21 W bulb included.



| Article No.      | EAN-Code 4007123... | UP | Cable length | Cable         | Output | Fittings | Voltage |
|------------------|---------------------|----|--------------|---------------|--------|----------|---------|
| <b>1 17269 3</b> | 576036              | 1  | 1,8 m        | H05RN-F 3G1,0 | 21 W   | GR10q    | 240 V   |

### Recommended accessories:

| Article No.      | EAN-Code 4007123... | UP | Description    | Output | Luminous flux | Lamp efficacy | Colour temperature | Colour rendering index | Fittings | Mercury content | Energy efficiency class |
|------------------|---------------------|----|----------------|--------|---------------|---------------|--------------------|------------------------|----------|-----------------|-------------------------|
| <b>1 17469 0</b> | 576241              | 1  | Jet-Light bulb | 21 W   | 1200 lm       | 57 lm/W       | 6400 K             | 80                     | GR10q    | 4 mg            | B                       |