



In-Line Stereo Jack



161-3300

KOBI CONN

In-Line Stereo Jacks



Circuit Diagram



Dimensions: In.

SPECIFICATIONS	
Type:	Hi-Rel, Shielded, In-Line Stereo
Breakdown Voltage:	500VAC for 1 Minute
Insulation Resistance:	100MΩ min. @ 500VDC
Contact Resistance:	50mΩ max.
Receptacle (1):	BSBM, Ni-P
Body (2):	PPO
Terminal (3):	PBS-EH, t=0.25, Au-P
Terminal (4):	PBS-EH, t=0.25, Ni-P
Terminal (5):	Steel, t=0.3, Ni-P
Cap (6):	BSBM, Ni-P
Strain Relief (7):	PVC, Black

Date Last Revised: 4-15-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300487

161-3300

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-3300](#)