






REV.	DATE	DESCRIPTION
A	01/25/04	UPDATE DRAWING FORMAT

RECOMMENDED
MOUNTING HOLE

RECOMMENDED CABLE STRIPPING DIM'S



NOTE:

1. CONTACT PIN TO SOLDER
OR CRIMPED CONTACT PIN
SQ. CRIMP SIZE 0.7(mm)
2. MAX. PANEL THICKNESS = 2.4mm

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8					DRAWN	G.R.S.	01/25/04						
7					CHECKED								
6									PART DESCRIPTION				
5	HEX NUT	BRASS	GOLD		1					SMB BULKHEAD DIRECT SOLDER JACK (FOR 0.85”, 0.86” CABLE)			
4	LOCK WASHER	BRASS	GOLD		1					PART NO.			
3	CONTACT PIN	BRASS	GOLD		1					142301			
2	INSULATOR	TEFLON	NATURAL		2					DWG. NO.			
1	BODY	BRASS	GOLD	1					142301.DWG		REV. A	SIZE A	SCALE NA
	DESCRIPTION	MATERIAL	FINISH	QTY			C:/142/142301.DWG						