


PRODUCT NUMBER

SEE TABLE



NOTES:

- ① MATERIAL: GLASS FILLED POLYAMIDE.
PART NUMBERS WITH A 'G' (963TC-NS12G) ARE A GRAYISH TAN AND MATCH THE 963T CONNECTORS.
PART NUMBERS WITH AN 'R' (963TC-LS12R) ARE A BROWNISH RED AND MATCH THE 963T2 CONNECTORS.
2. PART NUMBERS WITH 'NS' (963TC-NS12G) HAVE NO STRAIN RELIEF TABS.
3. SEE APPLICATION SPECIFICATION GS-20-004 FOR INSTRUCTIONS ON ASSEMBLY OF COVERS TO 963T AND 963T2 CONNECTORS.
- ④ PRODUCT NUMBERS WITH AN LF SUFFIX MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
5. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDERING PROCESSES.

mat'l. code SEE NOTE 1				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family FASTECH	
ltr	ecp no	dr	date	tolerances unless otherwise specified		INCH	title	
A	V81852	JRV	1998-10-20	angles	fin		963TC COVERS FOR 963T & 963T2 CONN.	
B	V12588	LSS	2001-10-25			scale 1:1	dwg no	
C	V05-0152	HTB	2005-03-04				sheet 1 of 3	
D	V06-0195	HTB	2006-03-10	dr	J.R. VOLSTORF	1998-10-20	size	
E	V06-0647	JRV	2006-07-06	enfr	J.R. VOLSTORF	1998-10-20	A92KC4077	
F	V07-0134	HTB	2007-02-16	chr	J.R. VOLSTORF	1998-10-20	type	
G	V08-0401	HTB	2008-12-12	appd	J.R. VOLSTORF	1998-10-20	CUSTOMER Drawing	
sheet	revision	G	G	G				
index	sheet	1	2	3				



PRODUCT NUMBER NOTE 4	LUCENT DEVICE CODE	LUCENT COMCODE	"A"	"B"	"C"	"D"	"E"
963TC-NS6G	TCOV-NS6G	106904899	2	0.250	0.00	0.00	.00
963TC-NS6GLF	-	-	2	0.250	0.00	0.00	.00
963TC-NS8G	TCOV-NS8G	106904907	3	0.375	0.00	0.00	.00
963TC-NS8GLF	-	-	3	0.375	0.00	0.00	.00
963TC-NS12G	TCOV-NS12G	106904915	5	0.625	0.00	0.00	.00
963TC-NS12GLF	-	-	5	0.625	0.00	0.00	.00
963TC-NS16G	TCOV-NS16G	106904923	7	0.875	0.00	0.00	.00
963TC-NS16GLF	-	-	7	0.875	0.00	0.00	.00
963TC-NS20G	O B S O L E T E						
963TC-NS20GLF	O B S O L E T E						
963TC-NS24G	TCOV-NS24G	106904956	11	1.375	0.00	0.00	.00
963TC-NS24GLF	-	-	11	1.375	0.00	0.00	.00
963TC-NS12R	TCOV-NS12R	106904618	5	0.625	0.00	0.00	.00
963TC-NS12RLF	-	-	5	0.625	0.00	0.00	.00
963TC-NS20R	O B S O L E T E						
963TC-NS20RLF	-	-	9	1.125	0.00	0.00	.00
963TC-NS24R	O B S O L E T E						
963TC-NS24RLF	-	-	11	1.375	0.00	0.00	.00
963TC-LS6G	TCOV-LS6G	106905425	2	0.250	0.20	0.30	.48
963TC-LS6GLF	-	-	2	0.250	0.20	0.30	.48
963TC-LS8G	TCOV-LS8G	106905433	3	0.375	0.20	0.30	.48
963TC-LS8GLF	-	-	3	0.375	0.20	0.30	.48
963TC-LS12G	TCOV-LS12G	106905458	5	0.625	0.30	0.50	.48
963TC-LS12GLF	-	-	5	0.625	0.30	0.50	.48
963TC-LS16G	TCOV-LS16G	106905466	7	0.875	0.30	0.50	.48
963TC-LS16GLF	-	-	7	0.875	0.30	0.50	.48
963TC-LS20G	O B S O L E T E						
963TC-LS20GLF	-	-	9	1.125	0.30	0.50	.48
963TC-LS24G	TCOV-LS24G	106905482	11	1.375	0.30	0.50	.48
963TC-LS24GLF	-	-	11	1.375	0.30	0.50	.48

mat'l. code				surface		tolerance		projection		product family	
SEE NOTES				ASME Y14.5		ASME Y14.5				FASTECH	
ltr	ec'n no	dr	date	tolerances unless otherwise specified							
G				angles				INCH		title	
								scale 1:1		963TC COVERS FOR 963T & 963T2 CONN.	
				dr	J.R. VOLSTORF	1998-10-20			dwg no		sheet 2 of 3
				engr	J.R. VOLSTORF	1998-10-20			A92KC4077		A4
				chr	J.R. VOLSTORF	1998-10-20			type		CUSTOMER Drawing
				appd	J.R. VOLSTORF	1998-10-20					
sheet index	revision sheet										



PRODUCT NUMBER NOTE 4	LUCENT DEVICE CODE	LUCENT COMCODE	"A"	"B"	"C"	"D"	"E"
963TC-LS6R	O B S O L E T E						
963TC-LS6RLF	-	-	2	0.250	0.20	0.30	.48
963TC-LS8R	O B S O L E T E						
963TC-LS8RLF	O B S O L E T E						
963TC-LS12R	TCOV-LS12R	106905359	5	0.625	0.30	0.50	.48
963TC-LS12RLF	-	-	5	0.625	0.30	0.50	.48
963TC-LS16R	O B S O L E T E						
963TC-LS16RLF	-	-	7	0.875	0.30	0.50	.48
963TC-LS20R	O B S O L E T E						
963TC-LS20RLF	-	-	9	1.125	0.30	0.50	.48
963TC-LS24R	TCOV-LS24R	106905391	11	1.375	0.30	0.50	.48
963TC-LS24RLF	O B S O L E T E						
963TC-LE20RLF	-	-	9	1.125	0.60	0.80	.25
963TC-NS6G-CB	O B S O L E T E						
963TC-NS8G-CB	O B S O L E T E						
963TC-NS12G-CB	O B S O L E T E						
963TC-NS16G-CB	O B S O L E T E						
963TC-NS20G-CB	O B S O L E T E						
963TC-NS24G-CB	O B S O L E T E						
963TC-LS6G-CB	O B S O L E T E						
963TC-LS8G-CB	O B S O L E T E						
963TC-LS12G-CB	O B S O L E T E						
963TC-LS16G-CB	O B S O L E T E						
963TC-LS6R-CB	O B S O L E T E						
963TC-LS8R-CB	O B S O L E T E						
963TC-LS12R-CB	O B S O L E T E						
963TC-LS16R-CB	O B S O L E T E						
963TC-LS20R-CB	O B S O L E T E						
963TC-LS24R-CB	O B S O L E T E						

mat'l. code SEE NOTES				surface ASME Y14.5	tolerance ASME Y14.5	projection 	product family FASTECH
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
G				angles	$\frac{R}{D}$	INCH	963TC COVERS FOR 963T & 963T2 CONN.
						scale 1:1	dwg no
				dr	T. BREWBAKER	2006-03-10	sheet 3 of 3
				engr	T. BREWBAKER	2006-03-10	size
				chr	T. BREWBAKER	2006-03-10	A4
				appd	T. BREWBAKER	2006-03-10	type
sheet index	revision sheet						CUSTOMER Drawing