





LOC	DIST	P	F	ZONE	LTR	REVISIONS	DATE	APPD
GP	00				H	REACTIVATE -1 PER 0S11-0004-04	09JAN04	CC



- 1 HOUSING: BLACK POLYESTER, UL 94V-0 RATED; CONTACT: BRASS PER MIL-C-50; INSERT: BRASS PER QQ-B-626.
- 2 GOLD PLATING PER MIL-G-45204, TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- 3 GOLD PLATED FOR A LENGTH OF 3.81[.150] MIN FROM MATING END, GOLD FLASH IN MATED AREA, 2.54μm[.000100] MIN TIN OR TIN-LEAD FOR A LENGTH OF DIMENSION A FROM OPPOSITE END, ALL OVER 1.27μm[.000050] MIN NICKEL.
- 4 GOLD PLATED FOR A LENGTH OF 3.81 [.150] FROM MATING END, 0.76μm [.000030] MIN GOLD IN MATED AREA, 2.54μm[.000100] MIN TIN OR TIN-LEAD FOR A LENGTH OF DIMENSION A FROM OPPOSITE END, ALL OVER 1.27μm[.000050] MIN NICKEL.



OBSOLETE	6.35	[.250]	4	745055-6
OBSOLETE	6.35	[.250]	3	745055-5
OBSOLETE	4.32	[.170]	4	745055-4
OBSOLETE	4.32	[.170]	3	745055-3
OBSOLETE	3.18	[.125]	4	745055-2
OBSOLETE	3.18	[.125]	3	745055-1

RECOMMENDED PC BOARD MOUNTING DIMENSIONS

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± 2'	DR 11-15-89 J McCLINTON	AMP AMP INCORPORATED Harrisburg, Pa. 17105		
MATERIAL	CHK 2-1-90 R.STONE	NAME PLUG ASSEMBLY, SIZE 5, 50 POSN, VERTICAL, AMPLIMITE® HD-20		
FINISH 2 CONTACT: SEE TABLE	APPD 2-2-90 S.SCHIEFERLY	SIZE C	CAGE CODE 00779	DRAWING NO 745055
	APPD 2-2-90 C.ROHDE	SCALE 4:1	SHEET 10F 1	
	PRODUCT SPEC 108-40025			
	APPLICATION SPEC -			
	WEIGHT -			