



68803-0004	HDMI TO DVI-D(M) CABLE ASS'Y,16.4FT	4999 ± 100	BLACK	7.3MM(TMDS - AWG#28)	887808276
68803-0003	HDMI TO DVI-D(M) CABLE ASS'Y,10FT	3048 ± 80	BLACK	7.3MM(TMDS - AWG#28)	887808276
68803-0002	HDMI TO DVI-D(M) CABLE ASS'Y,6.6FT	2012 ± 60	BLACK	7.3MM(TMDS - AWG#28)	887808276
68803-0001	HDMI TO DVI-D(M) CABLE ASS'Y,3.3FT	1006 ± 30	BLACK	7.3MM(TMDS - AWG#28)	887808276
MX P/N	DESCRIPTION	LENGTH	CABLE COLOR	CABLE OD	CABLE P/N

ENTER DESCRIPTION EC NO: DG2006-0075 DRWN: JFZHENG 2005/10/17 CHKD: JFZHENG 2005/10/19 APPR: DQLUO 2005/10/20	QUALITY SYMBOLS =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)	
---	-----------------------------	---------------------------------------	--

7 6 5 4 3 2 1

NOTE:

1. OVERMOLD SPECIFICATION:

1.1 DVI BOOT MOLDED SNOW WHITE PVC RESIN 887800076E~UL94V-0.

1.2 HDMI INNER MOLDED WITH PVC RESIN 887800019.

HDMI OUTER MOLDED WITH PVC RESIN 887800150.

1.3 DUST COVER MOLDED WITH PE 887800008.

2. MECHANICAL SPECIFICATIONE

2.1 CABLE SHOULD STAND THE PULL FORCE 89-111N FOR 30 SECONDS WITH NO VISIBLE TERMINATION DAMAGE.

2.2 CABLE SHOULD PASS THE FLEX TEST IN 100 CYCLES AT EACH OF PLANES, PER EIA 364-41, CONDITION 1.

3. DVI CONNECTOR SPECIFICATION:

4.1 REFER TO PRODUCT SPEC. PS74320-001.

4.2 CONTACT PLATING: AU FLASH.

4. CABLE CONSTRUCTION:

a.(AWG#28*1P+D)*4 + AWG#28*1P + AWG#28*3C, 7.3MMOD

"MOLEX" MUST BE IN CABLE MARKING.

5. MATERIAL MUST MEET MX ROHS STANDARD.

SHIELD	
--------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[68803-0004](#)