

GC-485 Series – Digital I/O Gage Heads



- RS-485 output
- $\pm 0.1\%$ of FR maximum ($\pm 0.05\%$ typical) linearity
- 32 devices communicating over 2 wires
- MIN, MAX and TIR readings
- Velocity output
- Internal tare (zero) function
- Stroke ranges from ± 0.125 to ± 1 inch
- IEC IP68 rating to 1,000 PSI [70 bars]

DESCRIPTION

The **GC-485 Series** heavy-duty, spring loaded gage heads are self-contained, ultra precision, digital I/O devices for high performance measurements in environments containing moisture, dirt, and fluid contaminants. The GC-485 eliminates the need for expensive and error-prone analog to digital conversion by internally converting the analog LVDT signals into engineering units (imperial or metric). The result is a fully calibrated and traceable measurement device, ready for installation, and 100% field interchangeable.

Operating on 8.5 to 30VDC supply, the GC-485 provides an addressable RS-485 loop output (MODBus RTU and ASCII protocols) running at 119kBd baud rate and capable of handling up to 32 devices communicating over two wires. MIN, MAX and TIR readings are sampled and stored internally at a maximum update rate of 600 samples per second, and are provided to the host on demand. A velocity output (inch or mm per second) is also available, while an internal tare (zero) function affords maximum measurement range flexibility.

These robust gage heads feature a removable black-chromed, hardened tool steel tip threaded (4-48UNF-2A) to the working end. Internal construction prevents the core and shaft from rotating as they move longitudinally. The welded electrical connector allows replacement of a damaged cable without sacrificing the sensor. The external $\frac{1}{2}$ -20 threads and the two supplied locknuts facilitate installation and adjustment.

Like in most of our LVDTs, the GC-485 windings are vacuum impregnated with a specially formulated, high temperature, flexible resin, and the coil assembly is potted inside its housing with a two-component epoxy. This provides excellent protection against hostile environments such as high vibration and shock.

The ruggedness, long life cycle, and very high reliability of the GC-485 provide a low cost of ownership over the life of the equipment onto which they are installed. The one-piece front end (barrel), machined from solid stainless steel bar, coupled with a bronze bushing, has far greater resistance to side loads compared to other designs; it reduces the risk of probe damage during installation or maintenance. The GC-485 design also require fewer parts and weld joints, thereby increasing overall structural integrity and reliability.

MEAS offers options, such as mating connector plugs, special contact tips (including AGD dial indicator tips), air-extend/spring retract, and cable assemblies. Also see our other models with built-in signal conditioning, **GCD** ($\pm$ DC voltage), **GCD-SE** (single-ended DC voltage), **GCT** (4-20mA, 2-wire loop); and the AC operated **GCA**.

Measurement Specialties, Inc. (NASDAQ MEAS) offers many other types of sensors and signal conditioners. Data sheets can be downloaded from our web site at: <http://www.meas-spec.com/datasheets.aspx>

MEAS acquired Schaevitz Sensors and the **Schaevitz™** trademark in 2000.

GC-485 Series – Digital I/O Gage Heads

FEATURES

- All-welded stainless steel construction
- MS type connector (MIL-C-5015)
- Hardened tool steel contact tip
- High side load resistance
- Programmable filtering
- Calibration certificate supplied with each unit
- Air extend/spring retract available (*consult factory*)

APPLICATIONS

- Roller Gap Control
- In-process Wet Grinding
- High Density Gaging
- Hand Held Gages
- X-Y Positional Feedback
- Remote Monitoring
- Applications where wiring must be minimized

PERFORMANCE SPECIFICATIONS

ELECTRICAL SPECIFICATIONS				
Parameter	GC-485 125	GC-485 250	GC-485 500	GC-485 1000
Stroke/gaging range	±0.125 [±3.17]	±0.25 [±6.85]	±0.5 [±12.7]	±1.0 [±25.4]
Input voltage	8.5 to 30 VDC			
Input current	50mA			
Output	RS-485 (MODBus RTU and ASCII protocols)			
Baud rate	119 kBd			
Output units	Imperial or Metric			
Resolution	15-bit, minimum			
Non-linearity	±0.1% of FR, maximum (±0.05% of FR, typical)			
Repeatability	25 µ-inch [0.6 µm]			
Stability	0.1% of FS			
Temperature coefficient of scale factor	0.025%/°F [0.045%/°C], maximum			
Frequency response (dynamic)	15Hz, maximum			

ENVIRONMENTAL SPECIFICATIONS & MATERIALS	
Operating temperature	-13°F to +185°F [-25°C to +85°C]
Survival temperature	-67°F to +203°F [-55°C to +95°C]
Shock survival	250 g (11ms half-sine)
Vibration tolerance	10 g up to 2kHz
Housing material	AISI 400 Series stainless steel
Electrical connector	6-pin MS type connector (MIL-C-5015)
IEC 60529 rating	IP68 to 1,000 PSI [70 bars] with use of proper mating connector plug

Notes:

All values are nominal unless otherwise noted

Dimensions are in inch [mm] unless otherwise noted

FR: Full Range is the stroke range, end to end; FR=2xS for ±S stroke range


GC-485 Series – Digital I/O Gage Heads

WIRING INFORMATION


Function	Connector pin
Power IN	E
Common	D
A (-Data)	A
B (+Data)	B

MECHANICAL SPECIFICATIONS

Parameter	GC-485 125	GC-485 250	GC-485 500	GC-485 1000
Stroke/gaging range	±0.125 [±3.17]	±0.25 [±6.85]	±0.5 [±12.7]	±1.0 [±25.4]
Pre-travel	0.28 [7.1]	0.18 [4.6]	0.20 [5.1]	0.10 [2.5]
Over-travel	0.29 [7.4]	0.03 [0.8]	0.35 [8.9]	0.10 [2.5]
Main body length "A"	4.90 [124.5]	5.76 [146.3]	7.46 [189.5]	9.42 [239.2]
Overall body length "B"	6.27 [159.3]	7.13 [181.1]	10.45 [265.4]	12.41 [315.2]
Plunger length "C" (fully extended)	7.30 [185.4]	8.16 [207.3]	12.93 [328.4]	14.87 [377.7]
Spring force	Typically 9oz [255 grams] at fully compressed electrical stroke			



REPLACEMENT/OPTIONAL CONTACT TIPS



Dimensions are in inch [mm]

GC-485 Series – Digital I/O Gage Heads

ORDERING INFORMATION

Description	Model	Part Number
±0.125 inch gage head <i>(Manual and software available on our web site)</i>	GC-485 125	02351012-000
±0.25 inch gage head <i>(Manual and software available on our web site)</i>	GC-485 250	02351013-000
±0.5 inch gage head <i>(Manual and software available on our web site)</i>	GC-485 500	02351014-000
±1.0 inch gage head <i>(Manual and software available on our web site)</i>	GC-485 1000	02351015-000
OPTIONS		
Air extend/spring retract gage head <i>(Consult factory)</i>	All GC Series	xxxxxxxx-150
ACCESSORIES		
DC power supply (15VDC)	PSD 40-15	02291339-000
Mating connector kit	PT06A-10-6S(SR)	62101011-000
Replacement contact tips	Contact Tip 2	67010005-000
	Contact Tip 3	67010006-000
	Contact Tip 4	67010002-000
	Contact Tip 5	67010007-000
	Contact Tip 6	67010008-000
	Contact Tip 7	67010009-000
	Contact Tip 8	67010010-000
	Contact Tip 9	67010001-000
	Contact Tip 10	67010011-000

Refer to our [“Options and Accessories for Gage Head”](#) data sheet.

Download the operation manual at: <http://www.meas-spec.com/manuals.aspx>

TECHNICAL CONTACT INFORMATION

NORTH AMERICA	EUROPE	ASIA
Measurement Specialties, Inc. 1000 Lucas Way Hampton, VA 23666 United States Phone: +1-800-745-8008 Fax: +1-757-766-4297 Email: sales@meas-spec.com Web: www.meas-spec.com	MEAS Deutschland GmbH Hauert 13 D-44227 Dortmund Germany Phone: +49-(0)231-9740-0 Fax: +49-(0)231-9740-20 Email: info.de@meas-spec.com Web: www.meas-spec.com	Measurement Specialties China Ltd. No. 26, Langshan Road High-tech Park (North) Nanshan District, Shenzhen 518057 China Phone: +86-755-33305088 Fax: +86-755-33305099 Email: info.cn@meas-spec.com Web: www.meas-spec.com

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.