



Multi 9 C60 UL 489 Listed 240 V Miniature Circuit Breakers

- UL 489 Listed and CSA 22.2 No. 5.1 for branch circuit protection
- Eliminates concerns and uncertainty of using a UL 1077 device where a UL 489 device is required
- Replaces fuses in low-ampere range; 17 ratings up to 35 A

Trip Curve	Use	Magnetic Release
C	For typical loads	7–10 x ampere rating (7–14 for DC)
D	For high inrush	10–14 x ampere rating

- 10 k AIR (1P @ 120 Vac; 2P and 3P @ 240 Vac)
- 60 Vdc for 1P and 125 Vdc for 2P (on C-curve circuit breakers only, see table below)
- Increased installation flexibility with standard box lugs or optional ring terminals
- Allows easy front-mounting and rear wiring when using ring terminals
- A wide range of electrical and mechanical accessories
- Suitable for reverse feeding
- Trip-free mechanism
- Positive indication of contact disconnect

Table 7.27: UL 489 Circuit Breakers (120/240 V)

Rating (A)	C Curve—7–10 Times Ampere Rating (7–14 DC)						D Curve—10–14 Times Ampere Rating					
	1P▲		2P■		3P		1P		2P		3P	
	Cat. No.	\$ Price	Cat. No.	\$ Price	Cat. No.	\$ Price	Cat. No.	\$ Price	Cat. No.	\$ Price	Cat. No.	\$ Price
Box Lug/Box Lug												
0.5	60100		60134		—	—	60117		60151		—	—
1	60101		60135		60168		60118		60152		60184	
1.5	60102		60136		60169		60119		60153		60185	
2	60103		60137		60170		60120		60154		60186	
3	60104		60138		60171		60121		60155		60187	
4	60105		60139		60172		60122		60156		60188	
5	60106		60140		60173		60123		60157		60189	
6	60107		60141		60174		60124		60158		60190	
7	60108		60142		60175		60125		60159		60191	
8	60109		60143		60176		60126		60160		60192	
10	60110		60144		60177		60127		60161		60193	
13	60111		60145		60178		60128		60162		60194	
15	60112		60146		60179		60129		60163		60195	
20	60113		60147		60180		60130		60164		60196	
25	60114		60148		60181		60131		60165		60197	
30	60115		60149		60182		60132		60166		60198	
35	60116		60150		60183		60133		60167		60199	
Ring Tongue/Ring Tongue												
0.5	60200		60234		—	—	60217		60251		—	—
1	60201		60235		60268		60218		60252		60284	
1.5	60202		60236		60269		60219		60253		60285	
2	60203		60237		60270		60220		60254		60286	
3	60204		60238		60271		60221		60255		60287	
4	60205		60239		60272		60222		60256		60288	
5	60206		60240		60273		60223		60257		60289	
6	60207		60241		60274		60224		60258		60290	
7	60208		60242		60275		60225		60259		60291	
8	60209		60243		60276		60226		60260		60292	
10	60210		60244		60277		60227		60261		60293	
13	60211		60245		60278		60228		60262		60294	
15	60212		60246		60279		60229		60263		60295	
20	60213		60247		60280		60230		60264		60296	
25	60214		60248		60281		60231		60265		60297	
30	60215		60249		60282		60232		60266		60298	
35	60216		60250		60283		60233		60267		60299	

- ▲ 1P dual rated 120 Vac/60 Vdc.
■ 2P dual rated 240 Vac/125 Vdc.

Interrupting ratings Page 7-3
Accessories Page 7-20
Dimensions Page 7-54
Mounting Bases Page 7-13
DIN Mounting Rail Section 18

