

Wiha Pico Soft Grip TORX®



267 TORX® Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	Size	mm	Inch	mm	Inch	pkg.
267 32	T1	40	1.6	134	5.3	10
267 33	T2	40	1.6	134	5.3	10
267 35	T3	40	1.6	134	5.3	10
267 36	T4	40	1.6	134	5.3	10
267 37	T5	40	1.6	134	5.3	10
267 39	T6	40	1.6	140	5.5	10
267 41	T7	40	1.6	140	5.5	10
267 43	T8	40	1.6	140	5.5	10
267 45	T9	50	2.0	150	5.9	10
267 47	T10	50	2.0	150	5.9	10
267 49	T15	60	2.4	160	6.3	10
267 51	T20	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



267 93 Set 8 Pcs. TORX® Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.	Size	mm	Size	mm	lbs.
267 93	267 32	T1 40	267 37	T5 40	.50
	267 33	T2 40	267 39	T6 40	
	267 35	T3 40	267 41	T7 40	
	267 36	T4 40	267 43	T8 40	



267 96 Set 8 Pcs. TORX® Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.	Size	mm	Size	mm	lbs.
267 96	267 37	T5 40	267 45	T9 50	.57
	267 39	T6 40	267 47	T10 50	
	267 41	T7 40	267 49	T15 60	
	267 43	T8 40	267 51	T20 60	

Wiha Pico Soft Grip Screw Holding



267 MagicSpring Screw Holding TORX® Screwdriver, With

Wiha-Precision Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
267 21	T6	40	1.6	140	5.5	.03	10
267 23	T7	40	1.6	140	5.5	.03	10
267 25	T8	40	1.6	140	5.5	.03	10
267 27	T9	50	2.0	150	5.9	.04	10
267 29	T10	50	2.0	150	5.9	.04	10
267 31	T15	60	2.4	160	6.3	.04	10

*Metric dimensions actual - Inch dimensions approximate



267 98 Set 6 Pcs. MagicSpring Screw Holding TORX®

Screwdriver, With Wiha-Precision Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips.

Item No.	Size	mm	Size	mm	lbs.
267 98	267 21	T6 40	267 27	T9 50	.45
	267 23	T7 40	267 29	T10 50	
	267 25	T8 40	267 31	T15 60	