


Insulated Test Accessories and Micro Clippers


"Micro Plunger Clips", Mini-Plunger Clip and Plunger Clip



Type BU-1010 test leads make difficult IC connections fast and easy. Spring-loaded beryllium copper conductor attaches to component leads and terminals. Type BU-1031 test clip to insulated mini-alligator clip. Type BU-1080 test clip to 0.025" (0.635) square pin receptacle. Type BU-1111, mini-plunger clip.

860-4618. BU-1010-A-24-0. Black, 24"	EACH 4.52	860-4628. BU-1031-A-36-0. Black, 36"	EACH 4.16
860-4619. BU-1010-A-24-2. Red, 24"	EACH 4.52	860-4630. BU-1031-A-36-2. Red, 36"	EACH 4.16
860-4620. BU-1010-A-36-0. Black, 36"	EACH 4.58	860-4632. BU-1080-E-12-0. Black, 12"	EACH 3.80
860-4622. BU-1010-A-36-2. Red, 36"	EACH 4.58	860-4634. BU-1080-E-12-2. Red, 12"	EACH 3.80
860-4624. BU-1031-A-24-0. Black, 24"	EACH 4.06	860-1124. BU-1111-A-24-0. Black, 24"	EACH 4.26
860-4626. BU-1031-A-24-2. Red, 24"	EACH 4.06	860-1125. BU-1111-A-24-2. Red, 24"	EACH 4.26

"Mini-Micro-Clipper" Test Clips



These clips are the smallest of the "Clipper" series. Type BU-1414 to 0.025" (0.635) diameter and smaller leads. Type BU-1420 to stackable banana plug. Type BU-1449 to tinned end wire. Type BU-1480 to 0.025" (0.635) square pin receptacle. Type BU-1481 to 0.025" (0.635) square pin.

860-4638. BU-1414-E-12-0. Black, 12"	EACH 5.25	860-4646. BU-1420-A-12-2. Red, 12"	EACH 5.20
860-4639. BU-1414-E-12-2. Red, 12"	EACH 5.25	860-4648. BU-1420-A-24-0. Black, 24"	EACH 5.30
860-4640. BU-1414-E-24-0. Black, 24"	EACH 5.30	860-4650. BU-1420-A-24-2. Red, 24"	EACH 5.30
860-4642. BU-1414-E-24-2. Red, 24"	EACH 5.30	860-4660. BU-1480-E-12-0. Black, 12"	EACH 4.21
860-4644. BU-1420-E-12-0. Black, 12"	EACH 5.20	860-4662. BU-1480-E-12-2. Red, 12"	EACH 4.21

Insulated Test Accessories

BU-4061-M-39/BU-4061-N-39
Shielded Banana Plug to Safety Test Prod — Silicone or PVC



Instrument end features a nine-leaf cage spring 4 mm shielded banana plug. Probe end has a stainless steel tip with 8-32 UNC thread to accept accessories such as BU-60TBO, BU-209, BU-225 or BU-226. Molded housing.

860-4718. BU-4061-M-39-0. Black	EACH 8.33
860-4720. BU-4061-M-39-2. Red	EACH 8.33
860-4722. BU-4061-N-39-0. Black	EACH 6.73
860-4724. BU-4061-N-39-2. Red	EACH 6.73


BU-4062-M-39/BU-4062-N-39
Shielded Right Angle Banana Plug to Safety Test Prod — Silicone or PVC



Instrument end features a 90° right angle nine-leaf cage spring 4 mm shielded banana plug. Probe end has a stainless steel tip with 8-32 UNC thread to accept accessories such as BU-60TBO, BU-209, BU-225 or BU-226. Molded housing.

860-4734. BU-4062-M-39-0. Black	EACH 8.59
860-4736. BU-4062-M-39-2. Red	EACH 8.59
860-4738. BU-4062-N-39-0. Black	EACH 6.99
860-4740. BU-4062-N-39-2. Red	EACH 6.99

BU-6162-M-39/BU-6162-N-39
Right Angle Shielded Banana Plug to Shielded Banana Plug — Silicone or PVC



Straight and right angle banana plugs have exclusive free rotation, nine-leaf beryllium copper, nickel-plated cage springs protected by rigid plastic sleeves. A constant positive contact with minimum resistance is provided by the plugs. Molded housing.

860-7506. BU-6162-M-39-0. Black	EACH 8.16
860-7508. BU-6162-M-39-2. Red	EACH 8.16
860-4726. BU-6162-N-39-0. Black	EACH 6.43
860-4728. BU-6162-N-39-2. Red	EACH 6.43


BU-6161-M-39/BU-6161-N-39
Shielded Banana Plugs — Both Ends — Silicone or PVC



Insulated banana plugs have exclusive free rotation, nine-leaf beryllium copper, nickel-plated cage springs protected by rigid plastic sleeves. A constant positive contact with minimum resistance is provided by the plugs. Molded housing.

860-6060. BU-6161-M-39-0. Black	EACH 7.96
860-6061. BU-6161-M-39-2. Red	EACH 7.96
860-4730. BU-6161-N-39-0. Black	EACH 6.17
860-4732. BU-6161-N-39-2. Red	EACH 6.17


BU-32601 Insulated Banana Couplings



Convenient couplings for extended test leads. It is designed to prevent unintentional disconnections. 4 mm banana plugs are accepted at both ends.


860-4614. BU-32601-0. Black	EACH 2.58
860-4716. BU-32601-2. Red	EACH 2.58

Kit 400008 Meter Mate™ M General Purpose Kit



Kit 400008 includes a carrying case (instrument mounted), insulated test lead, prod-to-banana (1 red, 1 black 1000 V), insulated plunger-hook, (1 red, 1 black, 1000 V), insulated banana jack to standard plug, (1 red, 1 black, 1000 V). Mueller's most popular threaded alligator clip with insulators (1 red, 1 black) 60.81

BU-26101 Insulated Plug-On Test Prod with Stainless Steel Tip



Accepts 4 mm insulated banana plugs. Positive contact up to 1000 V is provided by the high quality 0.08" (2 mm) stainless steel test point. The insulated body reduces risk of contact with voltage carrying parts with a tough safety shock guard collar.


Mech. Connection: 0.16" (4 mm) nickel-plated brass banana jack.
860-7526. BU-26101-0. Black

EACH 2.91

860-7528. BU-26101-2. Red

EACH 2.91

BU-26130 Ultra Tech Test Prod



Accepts both safety and uninsulated 4 mm banana plugs. The high quality polished stainless steel prod tip easily pierces lacquered and oxidized contact points up to 1000 V. Insulated body with safety shock guard collar reduces the risk of contact with voltage carrying parts. The slim-line prod design with clear Kynar® insulated sleeve allows for easy testing in confined areas.

Mech. Connection: 0.16" (4 mm) nickel-plated brass banana jack.



860-7522. BU-26130-0. Black

EACH 3.02

860-7524. BU-26130-2. Red

EACH 3.02

BU-65 Safety Crocodile Clip — 34 Amp



Fully insulated and molded from high-strength, glass-filled nylon. Plastic shrouds completely cover metal parts. Rated to 1000 V. The hinge and spring design permits wide jaw opening and high clamp pressure from a comparatively low-profile clip. A sharp tooth in the lower jaw of the clip prevents it from falling off when in operation.


860-7660. BU-65-0. Black

EACH 4.42

860-7661. BU-65-2. Red

EACH 4.42

BU-26106 Insulated Plug-On Test Prod with 8-32 Thread



Accepts 4 mm insulated banana plugs. Positive contact up to 1000 V is provided by the high quality 0.08" (2 mm) stainless steel test point.

The collar is flat on one side to prevent rolling. The insulated body reduces risk of contact with voltage carrying parts with a tough safety shock guard collar.


860-4702. BU-26106-0. Black

EACH 3.12

860-4704. BU-26106-2. Red

EACH 3.12

BU-20431 Right Angle Plunger Hook Clip — 1000 V, 3-Amp



Two tools in one, a BeCu contact hook and a probe tip with the plunger retracted. The hook extends 0.41" (10 mm) when fully depressed. The right angle lead connection accepts ultra-flex leads and numerous other insulated and conventional 0.16" (4 mm) banana plugs. The plunger body is fully insulated.

Mech. Connections: 0.16" (4 mm) insulated right angle jack.

860-7510. BU-20431-0. Black

EACH 5.10

860-7512. BU-20431-2. Red

EACH 5.10