

MATERIALS AND FINISHES

BODY ZINC ALLOY
PLATED NICKEL

HOUSING PLOYESTER BUTYLENE TEREPTALATE
COLOR: BLACK

CENTER CONTACT PHOSPHOR BRONZE
PLATED GOLD

INSULATOR POLYPROPYLENE (94-V2)

MOUNTING POST BRASS
PLATED TIN

SOLDER TAIL BRASS WIRE
PLATED TIN

LOCKWASHER PHOSPHOR BRONZE
PLATED NICKEL

JAM NUT BRASS
PLATED NICKEL

BNC JACK
INTERFACE

1/2-28 UNEF-2A

JAM NUT

LOCKWASHER

RECOMMENDED MOUNTING HOLE
PANEL THICKNESS: 5.50(.217) MAX
RECOMMENDED MOUNTING TORQUE:
0.56 N(5 INCH-LBS) MAX

RECOMMENDED PCB
CONFIGURATION

73171-6090	73100-0067 W/O NUT AND WASHER, PACKAGE BY TRAY
73171-2980	73100-0067, ONE PER BAG
73100-0067	PLASTIC TRAYS
PART NO.	PACKAGING

ES-73599-0000	INTERFACE
PS-73598-0051	PRODUCT SPECIFICATION
SPECIFICATION	DESCRIPTION

ADDED P/N 73171-6090

EC NO: URF2009-0317
2008/12/11
DRW:INLIN
2008/12/16
CHKD:
APPR:MHUANG
2008/12/16

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .---	± .---
3 PLACES	± .---	± .---
2 PLACES	± .---	± .---
1 PLACE	± .---	± .---

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY
C.M.HUNG

DATE
1993/02/01

CHECKED BY

DATE

APPROVED BY
KWH

DATE
1993/04/01

MATERIAL NO.

SEE TABLE

SIZE
C

SCALE
DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

BNC JACK, R/A, PCB
RECEPTACLE, 75 OHMS
BNC-J/RA/PCB

MOLEX INCORPORATED

DOCUMENT NO.
SD-73100-0067

SHEET NO.
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION