




LOC		DIST		REV		DATE		APPRO	
G	14	P	F	ZONE	LTR	DESCRIPTION	DATE	APPRO	
						REV 8 REDRAWN PER 0720-0040-93	2-2-93	18 DAP	



AMP		E13288	
WIRE RANGE		Listed	
22-16 AWG		22-16 AWG	
SOLID OR STRANDED		SOLID OR STRANDED	
LR7189 Certified		MILITARY P/N AND CLASS	
22-16 AWG		NOT APPLICABLE	
SOLID OR STRANDED			



△ STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928, COMMERCIAL WIRE RANGE IS 22-16

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
0.26-1.65mm² [509-3,260] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
WITHOUT NOTICE. THE ENGINEERING DEPARTMENT
SHOULD BE CONSULTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ±
3 PLC DEC ±
ANGLES

MATERIAL
COPPER PER
ASTM B-152
ANNEALED

FINISH
TIN PLATE
0.00254 [0.00100] MIN
THK PER MIL-T-10727

DR 2-2-93
TA BRINKMAN
CHK 2-2-93
DA PATTERSON

APPD 2-2-93
DE MILLER

APPD 2-2-93
JL MECKLEY

PRODUCT SPEC
APPLICATION SPEC

AMP
AMP Incorporated
Harrisburg, PA 17105-3608

TERMINAL, RING
TONGUE, SOLI STRAND™

SIZE
CAGE CODE
00779
DRAWING NO
322927

CUSTOMER DRAWING