





Mini-DIN PCB Shielded Jack

161-2303, 161-2304, 161-2305, 161-2306, 161-2307, 161-2308


KOBICONN

Mini-DIN PCB Shielded Jack


161-2303, 161-2304, 161-2305, 161-2306, 161-2307, 161-2308




3-Pin
161-2303







4-Pin
161-2304




5-Pin
161-2305




6-Pin
161-2306





DIMENSIONS: In.



7-Pin
161-2307



8-Pin
161-2308



SPECIFICATIONS

Rating:	100VAC 1A max. or 12VDC 2A max.
Insulation Resistance:	50MΩ min. @ 250VDC
Dielectric Strength:	250VAC for 1 minute
Contact Resistance:	30mΩ max.
Insertion Force:	.8Kg~5KGg
Withdrawal Force:	0.8Kg~4Kg
Life:	1,000 cycles

Date Last Revised: 6/22/05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300168