




Sensor cables

Connecting cables

M12 to M12
A-coded
shielded



Ordering data

Male, straight - Female, straight	
PUR halogen-free	1.5 m
Male, straight - Female, angled	
PUR halogen-free	1.5 m
Male, angled - Female, angled	
PUR halogen-free	1.5 m
Note	

3-pole

Type	Order No.
SAIL-M12GM12G-3S1.5Q	1058490150
SAIL-M12GM12W-3S1.5Q	1059470150
SAIL-M12WM12W-3S1.5Q	1059720150
Other versions on request	

4-pole

Type	Order No.
SAIL-M12GM12G-4S1.5Q	1058500150
SAIL-M12GM12W-4S1.5Q	1059480150
SAIL-M12WM12W-4S1.5Q	1059730150
Other versions on request	

5-pole

Type	Order No.
SAIL-M12GM12G-5S1.5Q	1058510150
SAIL-M12GM12W-5S1.5Q	1059540150
SAIL-M12WM12W-5S1.5Q	1059740150
Other versions on request	

Standard cable lengths

All cables listed under the ordering data have a length of 1.5 metres. The last four ordering digits must be changed when ordering other standard cable lengths.	1.5 m	xxxxxx0150
	3.0 m	xxxxxx0300
	5.0 m	xxxxxx0500
	10.0 m	xxxxxx1000

Technical data

Rated current	4 A
Protection class	IP 67
Core cross-section	0.34 mm²
Contact surface	gold-plated
Temperature range of housing	-25...+85 °C
Rated voltage	250 V (3- and 4-pole) / 125 V (5-pole)
(acc. to VDE standard 0110 ISO group C)	

Chapter W includes additional technical specifications for the cable

Dimensioned drawing

