



Product information

Erem®

530E12

Code No. : **T530E12**

Distance cutter

- Special tool steel
- ESD-safe
- Fixed cutting length
- Reduces mechanical shock on components

Technical Data

Cut:	Flush
Length:	120 mm / 4,724 Inch
Weight:	67 g / 2.36 oz.
Jaw length:	20 mm / .787 Inch
Width of tips:	3 mm / .118 Inch
Cutting length:	1,2 mm / .047 Inch
Max. cutting capability	
Copper wire:	Ø 1,2 mm / .047 Inch

Distance cutters

- Erem distance cutters are available with fixed and variable cutting lengths
- The tips are polished so as to prevent board damage
- For cutting wires to the right length and for fixing components

Erem Cutters and Tip Cutters

- Internal patented Erem Magic Spring
 - Reduce costs by long life
 - Constant spring force
 - Guarantees more than 1 million operations
- High precision screw joint
 - Smooth jaw action with no play

- Smooth cutting operation with no jaw overlapping
- Induction-hardened cutting edges in Rockwell hardness 63 - 65 HRc for exceptionally long life
- EMOS maximum opening stop
limits the cutting-edge tips from opening more than 5 mm / .197 Inch. The limited extent to which the handles can open prevent user hand fatigue.
- Ergonomically shaped handles
for high comfort, better grip and added safety
- Erem cut:
Options for semi flush, full flush or super flush cuts

Weller