


STANDARD & RUGGED USB 2.0

USB-A/USBR-A/USB-AM SERIES



SPECIFICATIONS

Insulator Material:

High Temperature
Thermoplastic

Contact Material:

Phosphor Bronze

Plating:

Gold on Contacts,
Nickel on Shell, Tin on Tails

Operating Temp Range:

-50 °C to +85 °C

Voltage Rating:

30 VAC

Cycles:

1500 (max tested)

Packaging:

Packaged and shipped in Bulk
Packaging Trays; Trays suitable
for automation available

Lead-Free Solderable:

-TH & -VU=Yes

(Wave Solder only)

TID Numbers (USB-A):

USB-A-D-X-X-TH (61001199)

USB-A-S-X-X-TH (61001180)

USB-A-S-X-X-SM2 (61001152)

TID Number (USB-AM):

USB-AM-S-X-X-SM (61001154)

SERIES	- A -	SHELL TYPE	PLATING	COLOR	TERMINATION
USB = Standard Connector		-S = Single	-F = Gold Flash on Mating Area, Tin on Tails	-B = Black (USB only)	-TH = Through-hole
USBR = Increased Retention Connector (Complies with Class 1, DIV II minimum withdrawal requirement of 15N.)		-D = Double (-TH option only)	-S = 30 μ" (0.76 μm) Gold on Mating Area, Tin on Tails	-W = White (USB only)	-SM2 = Surface Mount (USB only)
				-O = Orange (USBR only)	-VU = Upright, Through-hole

View complete specifications at: samtec.com?USB-A or samtec.com?USBR-A

USB	TYPE	SHELL TYPE	PLATING	COLOR	TERMINATION
	-AM = A Type (Plug)	-S = Single	-F = Gold Flash on Mating Area, Tin on Tails	-B = Black	-TH = Through-hole
			-S = 30 μ" (0.76 μm) Gold on Mating Area, Tin on Tails	-W = White	-SM1 = Surface Mount

View complete specifications at: samtec.com?USB-AM