







Printed Board Layout  
Component side

1) Einlötschäfte passend für Lochungen  
 $\varnothing 1 \pm 0.1$  nach IEC 60326-3  
 Solder pins for PCB connections  
 $\varnothing 1 \pm 0.1$  as per IEC 60326-3  
 A souder pour des trous de  $\varnothing 1 \pm 0.1$   
 selon IEC 60326-3

|                                      |                                                             |            |     |       |                                                                                       |                                               |                               |    |                   |                                                                                       |                |                    |                                                                                  |  |
|--------------------------------------|-------------------------------------------------------------|------------|-----|-------|---------------------------------------------------------------------------------------|-----------------------------------------------|-------------------------------|----|-------------------|---------------------------------------------------------------------------------------|----------------|--------------------|----------------------------------------------------------------------------------|--|
| A                                    | 09185067901                                                 | 3          | 4,5 |       |  | All Dimensions in mm<br>Original Size DIN A 3 |                               |    | Techn. Character. |                                                                                       |                |                    | Nicht tolerierte Maßel / Free size tolerances                                    |  |
|                                      | 09185066901                                                 | 2          | 4,5 |       |                                                                                       |                                               |                               |    |                   |                                                                                       |                |                    |                                                                                  |  |
|                                      | 09185065901                                                 | 0,76 µm Au | 4,5 |       |                                                                                       |                                               |                               |    |                   |                                                                                       |                |                    |                                                                                  |  |
|                                      | 09185067903                                                 | 3          | 2,9 |       |                                                                                       | 29759                                         | 29-MAR-02                     | CV | Detail.           | 01-DEC-99                                                                             | Th             | 1,5:1              | SEK 18 Male Connector Standard<br>06 poles<br>Angled pins<br>Long locking levers |  |
|                                      | 09185066903                                                 | 2          | 2,9 |       |                                                                                       | 29753                                         | 11-MAR-02                     | JB | Insp.             |                                                                                       |                |                    |                                                                                  |  |
|                                      | 09185065903                                                 | 0,76 µm Au | 2,9 |       |                                                                                       | 29739                                         | 03-DEC-01                     | JB | Stand.            |                                                                                       |                |                    |                                                                                  |  |
| Bestell-Nr.<br>Part-No.<br>Reference | Anforderungsstufe<br>performance level<br>Niveau de qualite | a          |     | 27931 | 15-JUNE-00                                                                            | JB                                            | HARTING EURL<br>F-95972 Paris |    |                   |  | TB 0918506x90x | Blatt/ page<br>2/2 |                                                                                  |  |
|                                      |                                                             |            |     | 26554 | 01-DEC-99                                                                             | JB                                            |                               |    |                   |                                                                                       |                |                    |                                                                                  |  |
|                                      |                                                             |            |     | Mod.  | Dat.                                                                                  | Name                                          |                               |    |                   |                                                                                       |                |                    |                                                                                  |  |