


REV.	DATE	DESCRIPTION
NC	11/02/05	INITIAL RELEASE
A	05/20/07	ADD END VIEW AND 9.65 FLATS DIM



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	G.R.S.	05/20/07						
7						CHECKED								
6						ISSUED				PART DESCRIPTION				
5										JACK TO PLUG THRU BNC ADAPTER				
4					SHEET	1 OF 1			PART NO.					
3	CONTACT PIN	PHOS. BRONZE	GOLD	1					112532–13–1					
2	INSULATOR	TEFLON	NATURAL	1										
1	HOUSING/BODY	BRASS	NICKEL	1										
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE		DWG. NO.			REV.	SIZE	SCALE
					DO NOT SCALE DRAWING		C:/112/112532–13–1.DWG		112532–13–1.DWG			A	A	NA