

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130106-0125](#)
Status: **Active**
Overview: [Stringlights](#)
Description: 10-Lantern Stringlight Cord Set Hand Lamps

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130106
NEMA Configuration	N/A
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Name	Woodhead®
Type	String Lights
UPC	78678834135
Woodhead	Yes

Physical

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	406.40mm (16.000")
Length	35.05m (115.0')
Material - Guard	N/A
Mounting Style	Stringer
Net Weight	14.160/kg
Packaging Type	Carton
Socket Construction	Rubber Molded

Electrical

Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Old Part Number	40-6156
-----------------	---------



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130106Series](#)