

Non-metallic Cord Connectors Straight Male N.P.T. & PG Thread

Low Profile



IP66
SUITABILITY



SEC100BA

Low Profile N.P.T. Cord Connectors

N.P.T. Hub Size	Cord Dia. Inches	(mm)	Color	Catalog Numbers	Non-metallic Locknuts
3/8"	.18"-.31"	(4.6-7.9)	Gray	SEC38GA*	31622002LPK50
3/8"	.18"-.31"	(4.6-7.9)	Black	SEC38BA*	31622002LPK50
1/2"	.17"-.45"	(4.3-11.4)	Gray	SEC50GA	31622003LPK50
1/2"	.17"-.45"	(4.3-11.4)	Black	SEC50BA	31622003LPK50
3/4"	.45"-.71"	(11.4-18.0)	Gray	SEC75GA	31622007LPK50
3/4"	.45"-.71"	(11.4-18.0)	Black	SEC75BA	31622007LPK50
1"	.59"-1.00"	(15-25.4)	Gray	SEC100GA	31622008LPK50
1"	.59"-1.00"	(15-25.4)	Black	SEC100BA	31622008LPK50

Note: See pages T-87 to T-91 for additional technical data and dimensional drawings.
Catalog numbers with PK50 suffix are bulk packed 50 pieces.



SECP29GA

Low Profile PG Cord Connectors

Hub Size	Cord Dia. Inches	(mm)	Color	Catalog Numbers	Non-metallic Locknuts
PG7	.11"-.25"	(2.9-6.4)	Gray	SECP7GA*	LNP7BPK100
PG7	.11"-.25"	(2.9-6.4)	Black	SECP7BA*	LNP7BPK100
PG9	.18"-.31"	(4.6-7.9)	Gray	SECP9GA*	LNP9BPK100
PG9	.18"-.31"	(4.6-7.9)	Black	SECP9BA*	LNP9BPK100
PG11	.23"-.40"	(5.8-10.0)	Gray	SECP11GA*	LNP11BPK100
PG11	.23"-.40"	(5.8-10.0)	Black	SECP11BA*	LNP11BPK100
PG13.5	.17"-.47"	(4.3-11.9)	Gray	SECP13GA	LNP13BPK100
PG13.5	.17"-.47"	(4.3-11.9)	Black	SECP13BA	LNP13BPK100
PG16	.23"-.53"	(5.8-13.5)	Gray	SECP16GA	LNP16BPK100
PG16	.23"-.53"	(5.8-13.5)	Black	SECP16BA	LNP16BPK100
PG21	.45"-.71"	(11.4-17.9)	Gray	SECP21GA	LNP21BPK100
PG21	.45"-.71"	(11.4-17.9)	Black	SECP21BA	LNP21BPK100
PG29	.59"-.99"	(15-25.2)	Gray	SECP29GA	LNP29BPK25
PG29	.59"-.99"	(15-25.2)	Black	SECP29BA	LNP29BPK25
PG36	.88"-1.30"	(22.2-32.0)	Gray	SECP36GA	LNP36BPK25
PG36	.88"-1.30"	(22.2-32.0)	Black	SECP36BA	LNP36BPK25



LNP29BPK25

Low Profile Metric Cord Connectors

Hub Size	Cord Dia. Inches	(mm)	Color	Catalog Numbers	Non-metallic Locknuts
M12	.12"-.25"	(2.9-6.4)	Gray	SECM12G	LNM12BPK100
M12	.12"-.25"	(2.9-6.4)	Black	SECM12B	LNM12BPK100
M16	.11"-.31"	(2.7-7.9)	Gray	SECM16G	LNM16BPK100
M16	.11"-.31"	(2.7-7.9)	Black	SECM16B	LNM16BPK100
M20	.17"-.45"	(4.3-11.4)	Gray	SECM20G*	LNM20BPK100
M20	.17"-.45"	(4.3-11.4)	Black	SECM20B*	LNM20BPK100
M25	.49"-.71"	(12.3-18.0)	Gray	SECM25G*	LNM25BPK100
M25	.49"-.71"	(12.3-18.0)	Black	SECM25B*	LNM25BPK100
M32	.59"-1.00"	(15.0-25.4)	Gray	SECM32G*	LNM32BPK100
M32	.59"-1.00"	(15.0-25.4)	Black	SECM32B*	LNM32BPK100
M40	.87"-1.30"	(22.0-32.0)	Gray	SECM40G	LNM40BPK100
M40	.87"-1.30"	(22.0-32.0)	Black	SECM40B	LNM40BPK100

Note: See pages T-87 to T-91 for additional technical data and dimensional data.
Catalog numbers above with "PK100" suffix, i.e. LNP7BPK100, are bulk packed 100 per carton.
Catalog numbers above with "PK25" suffix, i.e. LNP29BPK25, are bulk packed 25 per carton.
Items indicated with a * are UL recognized components.