

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings
- PDF-Vertical POU ..
- Specification Sheets
- PDF-32 and 48 Am ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Panduit POU ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'VB0D2B2BM30P1'

Your search criteria matched only one product, shown below

VB0D2B2BM30P1



Rack Mount Power Outlet Units

- Mounting brackets and screws included
- Integrated local power monitor display
- Power on indicator - green LED

▪ Part Number	VB0D2B2BM30P1
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Vertical power strip 32 A, 230V, 24 IEC C-13 and 6 IEC C-19 receptacles, two 16 A single pole magnetic breaker / on-off switch with integral switch guard, and a 3 meter power cord with a IEC 60309 – 2P+ E pin in sleeve connector. Complies with IEC 60950-1, EN 55022, EN 55024 and CE Marked. Dimensions: 66.3"H x 2.0"W x 2.0"D (1683mm x 51mm x 51mm)
▪ Product Type	Vertical Power Outlet Unit
▪ Color	Black
▪ Depth (In.)	2.0
▪ Depth (mm)	51
▪ Height (In.)	66.3
▪ Height (mm)	1683
▪ Width (In.)	2.0
▪ Width (mm)	51
▪ CE Compliant	Yes
▪ Plug Type	IEC 60309 - 2P+ E
▪ Pricing Description	Vertical, Mixed (24) C-13 & (6) C-19, 230V / 32A / Single-Phase POU
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ Voltage	230V
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.