




PRODUCT NO.	DESCRIPTION
73474-101	HEAT STAKE VERSION
73474-101LF	HEAT STAKE VERSION


FRONT VIEW



HEAT-STAKE
PEG VERSION



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE



NOTES:

- HOUSING MATERIAL: LCP, 30% GLASS FILLED
FLAME RETARDANT PER UL 94V-0.
COLOR: NATURAL
- INDICATED HOLES ARE UNPLATED.
- SEE SHEET 2 FOR PRESS-PEG VERSION.
SEE SHEET 3 FOR SCREW-DOWN VERSION.
- THE PRODUCTS WHERE THE PART NUMBER
ENDS IN "LF" MEET THE EUROPEAN UNION
DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.
ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C
FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN.

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family METRAL ACC
ltr	ecm	no	dr	date	tolerances unless otherwise specified	mm	title
G	v11668	LSS	6/12/01		angles	xx ±.01/.3	RECEPTACLE GUIDE MODULE, 5 ROW
H	v12868	CGD	1/02/02		linear	xxx ±.005/.13	
J	v05-0007	TAB	1/11/05		σ±2'	xxxx ±.0020/.050	scale 1:1
K	v05-0223	TAB	3/11/05	dr	M. FETROW	5/19/97	dwg no 73474
L	v05-0730	DAI	8/04/05	enr	C. PENDLETON	5/19/97	
M	M05-0231	MHT	10/28/05	chr	C. PENDLETON	5/19/97	sheet 1 of 5 A3
N	M06-0286	MNR	7/27/06	appd	C. PENDLETON	5/19/97	
sheet	revision	N	N	N	N	N	type
index	sheet	1	2	3	4	5	Product Customer Drawing

FRONT VIEW

PRESS PEG VERSION

REQUIRED PC BOARD LAYOUT COMPONENT SIDE

NOTES:

- HOUSING MATERIAL: LCP, 30% GLASS FILLED
FLAME RETARDANT PER UL 94V-0.
COLOR: NATURAL
- INDICATED HOLES ARE UNPLATED.
- THIS SHEET SHOWS DIMENSIONS OF OPTIONAL PRESS-PEG ONLY.
FOR ALL OTHER DIMENSIONS AND REQUIREMENTS SEE SHEET 1.
FOR HEAT-STAKE VERSION SEE SHEET 1, FOR SCREW-DOWN
VERSION, SEE SHEET 3.

mat'l. code
SEE NOTES

surface
ISO 1302 ✓
tolerance
ISO 406
ISO 1101

projection

mm
scale 1:1

product family
METRAL ACC

title
RECEPTACLE GUIDE
MODULE, 5 ROW

dr M. FETROW 5/19/97
enr C. PENDLETON 5/19/97
chr C. PENDLETON 5/19/97
appd C. PENDLETON 5/19/97

sheet index revision sheet


FCI

dwg no 73474 sheet 2 of 5 size A3




type Product Customer Drawing

PRODUCT NO.	DESCRIPTION
73474-301	SCREW DOWN VERSION
73474-301LF	SCREW DOWN VERSION

FRONT VIEW



SCREW DOWN
VERSION





REQUIRED P.C. BOARD LAYOUT
COMPONENT SIDE

NOTES:

- HOUSING MATERIAL: LCP, 30% GLASS FILLED
FLAME RETARDANT PER UL 94V-0.
COLOR: NATURAL
- THIS SHEET SHOWS DIMENSIONS OF OPTIONAL SCREW-DOWN ONLY.
FOR ALL OTHER DIMENSIONS AND REQUIREMENTS SEE SHEET 1.
FOR HEAT-STAKE VERSION SEE SHEET 1, FOR PRESS-PEG,
SEE SHEET 2.
- TWO MOUNTING SCREWS, P/N 63787-001, OR 63787-001LF FOR
73474-301LF, FOR MAX PCB THICKNESS 2.4mm [0.094"].
P/N 63787-002 OR 63787-002LF FOR 73474-301LF MAX
PCB THICKNESS 3.2mm [0.126"].
MUST BE ORDERED SEPARATELY
- THE MATING CONNECTOR FOR THIS APPLICATION MUST USE A
WALL-LESS HEADER HOUSING, P/N 63735-101, TO AVOID
INTERFERENCE WITH MOUNTING SCREW HEADS.

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family METRAL ACC
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
N					angles	linear	RECEPTACLE GUIDE MODULE, 5 ROW
					0°±2'	linear	scale 1:1
					dr	M. FETROW 5/19/97	dwg no
					enr	C. PENDLETON 5/19/97	sheet 3 of 5
					chr	C. PENDLETON 5/19/97	size A3
					app	C. PENDLETON 5/19/97	type Product Customer Drawing
sheet	revision						
index	sheet						



NOTES:


- ① HOUSING MATERIAL: LCP, 30% GLASS FILLED
FLAME RETARDANT PER UL 94V-0.
COLOR: NATURAL
2. THIS SHEET SHOWS DIMENSIONS OF OPTIONAL SCREW-DOWN ONLY.
FOR ALL OTHER DIMENSIONS AND REQUIREMENTS SEE SHEET 1.
FOR HEAT-STAKE VERSION SEE SHEET 1, FOR PRESS-PEG,
SEE SHEET 2.
3. TWO MOUNTING SCREWS, P/N 63787-001, OR 63787-001LF FOR
73474-301LF, FOR MAX PCB THICKNESS 2.4mm[0.094"].
P/N 63787-002 OR 63787-002LF FOR 73474-301LF MAX
PCB THICKNESS 3.2mm [0.126"].
MUST BE ORDERED SEPARATELY
4. THE MATING CONNECTOR FOR THIS APPLICATION MUST USE A
WALL-LESS HEADER HOUSING, P/N 63735-101, TO AVOID
INTERFERENCE WITH MOUNTING SCREW HEADS.

form: A3


PRODUCT NUMBER	DESCRIPTION
73474-401M	PRESS PEG VERSION
73474-401	PRESS PEG VERSION
73474-401LF	PRESS PEG VERSION

FRONT VIEW

PRESS PEG
VERSION



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE



NOTES:

- HOUSING MATERIAL: LCP, 30% GLASS FILLED
FLAME RETARDANT PER UL 94V-0.
COLOR: NATURAL
- INDICATED HOLES ARE UNPLATED.
- THIS SHEET SHOWS DIMENSIONS OF OPTIONAL PRESS-PEG ONLY.
FOR ALL OTHER DIMENSIONS AND REQUIREMENTS SEE SHEET 1.
FOR HEAT-STAKE VERSION SEE SHEET 1, FOR SCREW-DOWN
VERSION, SEE SHEET 3.

mat'l. code SEE NOTES	surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family METRAL ACC
ltr N	ecn no dr	date	angles linear	title RECEPTACLE GUIDE MODULE, 5 ROW
			0°±2'	dwg no 73474
			dr M. FETROW 5/19/97	sheet 5 of 5 size A3
			enr C. PENDLETON 5/19/97	
			chr C. PENDLETON 5/19/97	
			app C. PENDLETON 5/19/97	
sheet index	revision sheet			type Product Customer Drawing