

Panel mounting base - RC-0000000WQ00 - 1593021

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Panel mounting base, series: RC, straight, Screw locking, M23, Radial O-ring, 4x Ø2,7, shielded: yes, panel thickness min.: 3 mm

RoHS

IP67

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 193832
GTIN	4046356193832
Weight per Piece (excluding packing)	25.750 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

General

Type of locking	Screw locking
Pg housing screw connection	none
Mounting type	4x Ø2,7

Ambient conditions

Ambient temperature	-20 °C ... 125 °C
Degree of protection	IP67

Material

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Gasket and O-ring material	FPM

Specifications according to DIN EN 61984:2001

Panel mounting base - RC-0000000WQ00 - 1593021

Technical data

Specifications according to DIN EN 61984:2001


Installation height max.	2000 m
--------------------------	--------

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values


Drawings

Diagram




Panel mounting base - RC-0000000WQ00 - 1593021

Diagram




Dimensional drawing



Panel mounting base - RC-0000000WQ00 - 1593021

Dimensional drawing



Installation dimensions
Flat gasket, radial O-ring

Classifications

eCl@ss

eCl@ss 10.0.1	27440202
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440202
eCl@ss 8.0	27440202

Panel mounting base - RC-0000000WQ00 - 1593021

Classifications

eCl@ss

eCl@ss 9.0	27440202
------------	----------

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC000437
ETIM 6.0	EC000437
ETIM 7.0	EC000437

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.01742
-----	---	---------