



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT<br>PART NO. | NOMINAL<br>I.D.  | BUNDLE DIA.                      | NO. OF<br>CARRIERS | NO. OF<br>STRANDS<br>PER CARRIER | WEIGHT<br>/1000'<br>lbs. (kg) |
|---------------------|------------------|----------------------------------|--------------------|----------------------------------|-------------------------------|
| SE12____-R__        | 0.125<br>(3.18)  | 0.0937 - 0.25<br>(2.37 - 6.35)   | 32                 | 1                                | 1.81 (82)                     |
| SE25____-R__        | 0.250<br>(6.35)  | 0.125 - 0.375<br>(3.17 - 9.53)   | 24                 | 3                                | 3.92 (1.78)                   |
| SE38____-R__        | 0.375<br>(9.53)  | 0.1875 - 0.500<br>(4.76 - 12.70) | 36                 | 3                                | 5.71 (2.59)                   |
| SE50____-R__        | 0.500<br>(12.70) | 0.25 - 0.75<br>(6.35 - 19.05)    | 48                 |                                  | 7.41 (3.37)                   |
| SE75____-R__        | 0.750<br>(19.05) | 0.5 - 1.25<br>(12.70 - 31.75)    | 64 or 72           |                                  | 10.42 (4.74)                  |
| SE125____-R__       | 1.250<br>(31.75) | 0.75 - 1.5<br>(19.05 - 38.10)    | 96                 |                                  | 15.87 (7.21)                  |
| SE150____-R__       | 1.500<br>(38.10) | 1.0 - 2.125<br>(25.40 - 53.98)   |                    | 4                                | 19.61 (8.91)                  |
| SE175____-R__       | 1.750<br>(44.45) | 1.25 - 2.75<br>(31.75 - 69.85)   | 120                |                                  | 23.3 (10.59)                  |
| SE200P-_-R_-        | 2.000<br>(50.80) | 1.50 - 3.50<br>(38.10 - 88.90)   | 120                |                                  | 33.3 (15.10)                  |
| SE250P-_-R_-        | 2.500<br>(63.50) | 1.750 - 3.635<br>(44.50 - 92.33) | 120                |                                  | 6                             |



NOTES:

- ALL STRANDS OF THE PET SLEEVING SHALL BE THE SAME COLOR.
- THE FLAME RETARDANT PET MATERIAL SHALL HAVE ALL STRANDS THE SAME COLOR EXCEPT FOR TWO CRISSCROSS WHITE TRACERS (EACH TRACER CONSISTING OF ONE COMPLETE CARRIER) OR ONE SINGLE STRAND TRACER (ONE STRAND WITHIN CARRIER IS THE OPPOSITE COLOR). ALL STRANDS OF WHICH ARE WHITE, EXCEPT FOR WHITE SLEEVING, THE TRACERS ARE THEN BLACK.
- REELS MAY HAVE SPLICES, DEPENDING ON LENGTH:



| LENGTH      | 50 FT | 100 FT | 200 FT | 500 FT | 1000 FT |
|-------------|-------|--------|--------|--------|---------|
| MAX SPLICES | 0     | 1      | 1      | 2      | 3       |

- SE200P & SE250P ARE ONLY OFFERED IN THE STD PET MATERIALS.

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

CAD FILENAME/LAYERS

G03597BX\_DC\_GB0239KD/OOF

**PANDUIT**

CORP. TINLEY PARK, ILLINOIS

STANDARD BRAIDED  
EXPANDABLE SLEEVING (SE)  
(CUSTOMER DRAWING)

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:

(.X) ± N/A (XXX) ± N/A  
(.XX) ± N/A ANGLES ± N/A

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
TMSA

DATE  
3/17/05

CHK'D

MAT'L:  
SEE  
PART NUMBER  
DESCRIPTION

SCALE NONE

DRAWING NO.

GB0239KD

DWG

A  
SIZE

|     |          |      |     |                                                                                                                                                                                     |          |      |      |
|-----|----------|------|-----|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|------|------|
| OOF | 3-27-12  | LEF  | VJS | H: RE-ADDED PANDUIT PART NUMBERS SE200P&SE250P<br>G: ADDED "CUSTOMER DRAWING" TO TITLE DESCRIPTION<br>F: ADDED NOTE #3, #4 AND TABLE.                                               | GB0239KD | OOF  | RAMI |
| OOE | 12-19-11 | LEF  | VJS | E: REMOVED NOTE #3 FROM NOTES.<br>D: REMOVE COLOR "C" CLEAR<br>C: REMOVE PARTS SE200P-R AND SE250P-R<br>B: REPLACE TOLERANCING WITH N/A<br>A: MATERIAL CHANGED TO PART# DESCRIPTION | GB0239KD | OOE  | RAMI |
| OOD | 10-11-09 | TMSA |     | CHANGED UPPER BUNDLE DIAMETER FOR<br>THE FOLLOWING SE38 FROM .625 ,<br>SE150 FROM 2.250, & SE250 FROM 4.500<br>REMOVED NOTE 3 AND RENUMBERED NOTES.                                 | GB0239KD | OOD  |      |
| REV | DATE     | BY   | CHK | DESCRIPTION                                                                                                                                                                         | ECN - R  | CUST | SUP  |