


BURNDY® Products FCI

Cable Ties

UNIRAP™

STANDARD CABLE TIES (Continued)



120 Lb. Minimum Tensile Strength

STANDARD PACKAGE CATALOG NUMBER	MATERIAL	MAXIMUM BUNDLE DIAMETER In. [mm]	MINIMUM TENSILE STRENGTH Lbs. (N)	LENGTH In. [mm]	WIDTH In. [mm]	INSTALLATION TOOL	TOOL SETTING	BULK PACKAGE CATALOG NUMBER
CT120200L	Natural Nylon 6/6	2.00 [51]	120 (534)	8.87 [226]	.30 [7.6]	TWT2, MK9	Standard	CT120200D
CT120200L0	Black Nylon 6/6 UV							CT120200D0
CT120300L	Natural Nylon 6/6	3.00 [76]		11.87 [302]				CT120300D
CT120300L0	Black Nylon 6/6 UV							CT120300D0
CT120400L	Natural Nylon 6/6	4.00 [102]		15.25 [387]				CT120400D
CT120400L0	Black Nylon 6/6 UV							CT120400D0
CT120900L	Natural Nylon 6/6	9.00 [229]		29.75 [776]				CT120900D
CT120900L0	Black Nylon 6/6 UV							

175 Lb. Minimum Tensile Strength



STANDARD PACKAGE CATALOG NUMBER	MATERIAL	MAXIMUM BUNDLE DIAMETER In. [mm]	MINIMUM TENSILE STRENGTH Lbs. (N)	LENGTH In. [mm]	WIDTH In. [mm]	INSTALLATION TOOL	TOOL SETTING	BULK PACKAGE CATALOG NUMBER
CT175400Q	Natural Nylon 6/6	4.00 [102]	175 (778)	15.00 [381]	.35 [8.9]	TWT2, MK9	Heavy	
CT175400Q0	Black Nylon 6/6 UV							
CT175600Q	Natural Nylon 6/6	6.00 [152]		21.00 [533]				
CT175600Q0	Black Nylon 6/6 UV							
CT175900Q	Natural Nylon 6/6	9.00 [229]		32.00 [813]				
CT175900Q0	Black Nylon 6/6 UV							
CT1751100Q	Natural Nylon 6/6	11.00 [279]		36.00 [914]				
CT1751100Q0	Black Nylon 6/6 UV							
CT1751400Q	Natural Nylon 6/6	14.00 [356]		52.00 [1321]				
CT1751400Q0	Black Nylon 6/6 UV							

K-7

250 Lb. Minimum Tensile Strength



STANDARD PACKAGE CATALOG NUMBER	MATERIAL	MAXIMUM BUNDLE DIAMETER In. [mm]	MINIMUM TENSILE STRENGTH Lbs. (N)	LENGTH In. [mm]	WIDTH In. [mm]	INSTALLATION TOOL	TOOL SETTING	BULK PACKAGE CATALOG NUMBER
CT250600Q	Natural Nylon 6/6	6.00 [152]	250 (1112)	23.00 [584]	.50 [12.7]	TWT2, MK9	Heavy	
CT250600Q0	Black Nylon 6/6 UV							
CT250800Q	Natural Nylon 6/6	8.00 [203]		29.00 [737]				
CT250800Q0	Black Nylon 6/6 UV							
CT2501000Q	Natural Nylon 6/6	10.00 [254]		35.00 [889]				
CT2501000Q0	Black Nylon 6/6 UV							
CT2501200Q	Natural Nylon 6/6	12.00 [305]		40.00 [1016]				
CT2501200Q0	Black Nylon 6/6 UV							