

Cover plate - HC-B 10-AP-GY - 1660371

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

HEAVYCON cover plate, for panel cutouts of type B10/HV3, 3.5 mm thick, gray



RoHS

Key Commercial Data

Packing unit	10 STK
GTIN	 4 017918 022013
GTIN	4017918022013

Technical data

Dimensions

Length	103 mm
Height	3.5 mm
Hole diameter	4.5 mm
Width	52 mm
Drill hole distance, horizontal	83 mm
Drill hole distance, vertical	32 mm

General

Note	For panel cutouts of type B10/HV3
Material	PA
Flammability rating according to UL 94	HB
Color	gray
Type	B10 / HV3

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
------------	---


Cover plate - HC-B 10-AP-GY - 1660371

Technical data

Environmental Product Compliance

	No hazardous substances above threshold values
--	--

Drawings



Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>