

Industrial Adhesives & Tapes

- Products
- Applications
- Industries
- Capabilities
- Support
- Where to Buy

[United States](#) > [All 3M Products](#) > [Manufacturing](#) > [Industrial Adhesives & Tapes](#) > [Adhesives - Wind](#) > 3M™ Scotch-Weld™ Epoxy Adhesive 3501 Gray Part B/A, 2 fl oz Kit, 6 Kits per case

3M™ Scotch-Weld™ Epoxy Adhesive 3501 Gray Part B/A, 2 fl oz Kit, 6 Kits per case

3M ID 62350105300    UPC# 00021200208423    Part Number 3501    3M Product Number 3501

Print

Share



★★★★★

[Write a review](#)

3M™ Scotch-Weld™ Epoxy Adhesive 3501 is a rigid, two-part epoxy adhesive. 1:1 mix ratio, 6-10 minute work life and handling strength in approximately 25 minutes. This kit contains 2 fl. oz. of part B and 2 fl. oz. of part A.

Where to Buy

Need Help?

Questions?

We can help

[Contact Us](#)

Overview

Documents

Reviews

3M™ Scotch-Weld™ Epoxy Adhesive 3501 is used in bonding metals, wood, and plastics.

Specifications

Adhesive Type	Epoxy
Applications	Hard Disk Drive Component Assembly
Brand	Scotch-Weld
Color	Gray
Consumer Label	No
Container Volume	2 fl oz (US)
Full Cure	48 Hours @ 72 F (22 C)
Hardness	75-80 Shore D
Industries	Transportation , Specialty Vehicle , Construction , Military & Government , General Industrial , Electronics , Consumer Goods
Mix Ratio Volume Base:Accelerator	1 : 01
Peel Strength at 72 Degrees F (22 Degrees C)	4 lb/in
Physical Form	Paste
Product Form	Kit
Shear Strength at 72 Degrees F (22 Degrees C)	2400 Pound-Force Per Square Inch
Shelf Life in Months (from date of manufacture)	24
Specific Gravity	1.47
Storage Temperature	72 Degree Fahrenheit
Substrate 1	Metal , Glass & Ceramics
Substrate 2	Metal , Glass & Ceramics
Time to Handling Strength	25 Minute
Type	Epoxy Adhesive
Worklife	7 minutes @ 72 F (22 C)