



FILE NO.



SPECIFICATION:

- Frequency Response : 10Hz-50KHz,+/- .5dB@+4dBu
- THD : .01% typical@1KHz,+18dBu,
<.05%@100Hz,+24dB
- Insertion Loss : 4dB@100k Ohm Load, 5.5dB@600 Ohm Load
- Connections : XLR Male and RJ45 balanced/unbalanced jack
- Power Requirements : Passive
- Dimension(LxWxH) : 88.9mmx63.5mmx38.1mm

4	RJ45 JACK	1		
3	XLR MALE	2		
2	CUSHION	4	RUBBER	
1	IRON CASE	1	SPCC THICKEST:1.2mm	
NO.	NAME	Q'TY	MATERIAL	NOTE

UNIT: mm

TOLERANCE
X ±0.25
XX ±0.1
XXX ±0.05
ANGLES ±1°

TITLE:

Two channel balanced audio balun
male XLR connectors

50-7728

MCM Custom Audio
MCM, an InOne company
650 Congress Park Drive
Centerville Ohio 45459
www.mcmnone.com

DWG NO.

SCALE: 1/1

SHEET of

REVISION DATE

DATE

CHECKED

APPROVED

DATE JUL/19/2006

DATE

DATE