






LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			K1	REVISED PER ECO-10-000443	11JAN10	KK	AEG



- NOTES:
- POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE OF BEAMS).
- TOLERANCE NON-CUMULATIVE.
- THE MATING END OF THE CONTACT IS IDENTIFIED BY THE LETTER "A" STAMPED ON THE RECEPTACLE BOX.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

RECOMMENDED BOARD MOUNTING
(RECOMMENDED BOARD THICKNESS: .055-.070)



	3.120	2.964	20	2-87982-0
	2.964	2.808	19	1-87982-9
	2.808	2.652	18	1-87982-8
	2.652	2.496	17	1-87982-7
	2.496	2.340	16	1-87982-6
	2.340	2.184	15	1-87982-5
	2.184	2.028	14	1-87982-4
	2.028	1.872	13	1-87982-3
	1.872	1.716	12	1-87982-2
	1.716	1.560	11	1-87982-1
	1.560	1.404	10	1-87982-0
	1.404	1.248	9	87982-9
	1.248	1.092	8	87982-8
	1.092	.936	7	87982-7
OBSOLETE	.936	.780	6	87982-6
OBSOLETE	.780	.624	5	87982-5
OBSOLETE	.624	.468	4	87982-4
OBSOLETE	.468	.312	3	87982-3
	.312	.156	2	87982-2
	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L D RINGLEY 17MAR86	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK P deJONG 18MAR86		
		APVD P deJONG 18MAR86		
		PRODUCT SPEC 108-25,016		
MATERIAL HOUSING-FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK CONTACTS- PHOS BRONZE		APPLICATION SPEC 114-25,004	WEIGHT -	SIZE A2
FINISH .000030 GOLD IN THE CONTACT AREA, GOLD FLASH ON THE REMAINDER, ALL OVER .000050 NICKEL		NAME ASSY, MOD I, BOARD MOUNT RECP, .156 CL , STD PRESSURE, TYPE B, FOR RECTANGULAR HOLE MOUNTING		RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1
			REV K1	