



REV.	DATE	DESCRIPTION
NC	05/22/03	INITIAL RELEASE



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.						05/22/03
7	COVER	BRASS	GOLD	1		CHECKED			PART DESCRIPTION SMA R/A DIRECT SOLDER PLUG (FOR .141” SEMI-RIGID CABLE)				
6	GASKET	SILICONE	RED	1		ISSUED							
5	RETAINER RING	BER. COPPER	NATURAL	1		SHEET	1 OF 1		PART NO. 132112				
4	CONTACT PIN	BRASS	GOLD	1									
3	INSULATOR	TEFLON	NATURAL	1					DWG. NO. 132112.DWG REV. NC SIZE A SCALE NA				
2	BODY	BRASS	GOLD	1									
1	SHELL	BRASS	GOLD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE	C:/132/132112.DWG						