

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100035](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Wet Location 70W Metal Halide Magnet Mount Area Light, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0')

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E174254

General
Product Family Portable Lighting
Series [130110](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 3
Outlet None
Overview [Wide-Area Lighting Products](#)
Product Name Woodhead
Type Wide Area Lamps
UPC 78678829248

Physical
Cord Length - Primary 3.04m (10.0')
Cord Length - Secondary N/A
Depth 207.26mm (8.160")
Duty Wet Location
Guard Included No
Guard Type N/A
Height 264.16mm (10.400")
Length 228.60mm (9.000")
Material - Globe Clear Polycarbonate
Material - Guard N/A
Mounting Style Magnet
Net Weight 5406.821/g
Packaging Type Carton
Socket Construction N/A

Electrical
Bulb Type Metal Halide - Probe Start
Cord Type - Primary 16/3 SJTOW
Lamp Type MH70
Lamp Wattage - Maximum 70W
Lumens 3600
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info
Engineering Number 8565-MH



EU ELV
Not Relevant

EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130110 Series](#)