

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [45626-0001](#)
Status: **Active**
Overview: SPOX™ BMI
Description: 2.50mm Pitch SPOX™ BMI Plug Housing, Dual Row, Panel Mount, 6 Circuits

Documents:

3D Model	Product Specification PS-45579-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
TUV	30682035.001
UL	E29179

General

Product Family	Crimp Housings
Series	45626
Application	Signal, Wire-to-Wire
MolexKits	Yes
Overview	<u>SPOX™ BMI</u>
Product Name	SPOX BMI™
UPC	822348232314

Physical

Circuits (maximum)	6
Color - Resin	Black
Flammability	94V-0
Gender	Male
Glow-Wire Compliant	No
Lock to Mating Part	None
Material - Resin	Polyester
Net Weight	2.199/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C


Electrical

Current - Maximum per Contact	3A
-------------------------------	----

Material Info

Reference - Drawing Numbers

Product Specification	PS-45579-001
Sales Drawing	SD-45626-001



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[45626Series](#)

Mates With

[45579 SPOX™ BMI Receptacle Housing](#)

Use With

[456270002 SPOX™ Male Crimp Terminal](#)