



DO NOT SCALE
FROM THIS PRINT

NOTES:

1. C REPRESENTS A CRITICAL DIMENSION.
2. PUSHOUT FORCE TO BE: 2 lb. (32oz) MIN.
3. ORIENTATION OF PART IN T&R MAY VARY DEPENDING ON POCKET.
4. MAX CUT FLASH .030 ON TAIL AND POST.
5. DUE TO THE HIGH AMOUNT OF INSERTION FORCE NEEDED, THE -LC OPTION IS NOT COMPATIBLE WITH AUTO PLACEMENT. SAMTEC RECOMMENDS MANUAL PLACEMENT FOR ALL ASSEMBLIES WITH THE -LC OPTION.
6. AVAILABLE ON -01 LEAD STYLE ONLY, MATES WITH SSW, SSQ, SSM, BCS, ESW, ESQ.
7. 50 POSITION PARTS ARE ONLY AVAILABLE FOR INTERNAL SAMTEC USE ONLY.
8. NOTE DELETED.



PLATING SPEC.

- T: MATTE TIN ON ENTIRE PIN
- S: 30μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- G: 10μ" SELECTIVE GOLD IN CONTACT AREA, 3μ" SELECTIVE GOLD ON TAIL
- L: 10μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- F: 3μ" SELECTIVE GOLD IN CONTACT AREA, 3μ" SELECTIVE GOLD ON TAIL
- H: 30μ" SELECTIVE GOLD IN CONTACT AREA, 3μ" SELECTIVE GOLD ON TAIL
- TL: TIN/LEAD (90/10+/-5%) CONTACT AND TAIL (-01 LEAD STYLE ONLY)
- STL: 30μ" SELECTIVE GOLD IN CONTACT AREA, TIN/LEAD (90/10+/-5%) (LEAD STYLE -01 & -02 ONLY)
- TM: MATTE TIN CONTACT AND TAIL
- SM: 30μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- LM: 10μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- FM: 3μ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- SS: 30μ" STRIPE SELECTIVE GOLD IN CONTACT AREA, MATTE TIN TAIL (SEE NOTE 6)

TSM-1XX-XX-XXX-SH-XX-XXX-XX

No. OF POSITIONS
-02 THRU -36,
50 (SEE NOTE 7)LEAD STYLE
SEE TABLE 1

OPTION #3

- P: PICK & PLACE PAD (SEE FIG 3)
USE PPP-08 (-04 THRU -36 POSITION OR 02 & 03 POSITION WITH -TR ONLY)
- TR: TAPE & REEL (-02 THRU -30 POSITION) (LEADS MAY NOT BE VISIBLE FOR CUSTOMER VISUAL INSPECTION ON SMALLER POSITION PARTS WHEN USED WITH -P OPTION.)
- K: POLYIMIDE FILM (SEE FIG 6, SHT 2) (-04 THRU -36 POSITION) (-02 & -03 POSITIONS WITH -TR ONLY) (USE K-DOT-.197-.344-.005)

OPTION #2

- XXX: POLARIZED POSITION SPECIFY OMITTED PIN

OPTION #1

- LC: LOCKING CLIP (SEE FIG 1) (SEE NOTE 5)
USE LC-09-TM (-03 THRU -36 POS USE 2 PER STRIP) (-02 POS USE 1 PER STRIP) (USE TSM-50-SHU)
- A: ALIGNMENT PIN
(USE TSM-XX-SHU-XX BODY FOR MOLDED -A PINS, POS -02 THRU -50, SEE FIG 2, SHEET 2)
(USE TSM-50-SHU BODY FOR STAKED -A PINS, POS -04 THRU -50, SEE FIG 4, SHEET 2)


LEAVE BLANK FOR NO HOLD
DOWN OPTION (USE TSM-50-SHU SEE FIG 1,
CAN BE CUT TO POSITION) N/A ON STYLE -03

ROW SPECIFICATION
-SH: SINGLE HORIZONTAL

TABLE 1			
LEAD STYLE	"B"	TERMINAL	"C"
-01	.230 [5.84]	T-1S6-08-X-2	.180 [4.57]
-02	.320 [8.13]	T-1S6-15-X-2	.190 [4.83]
-03	.420 [10.67]	T-1S6-09-X-2	.190 [4.83]
-04	.120 [3.05]	T-1S6-07-X-2	.190 [4.83]

DIFFERENT AS SHOWN. OTHERWISE SAME AS FIG 1

TABLE 3	
POS.	"E"
ODD	.150 [3.81]
EVEN	.100 [2.54]



$$\text{FOR ODD: "A"} = \frac{(\text{NO. OF POS X .100 [2.54]} - .300 [7.26])}{2}$$

$$\text{FOR EVEN: "A"} = \left[\frac{(\text{NO. OF POS X .100 [2.54]} - .300 [7.26])}{2} \right] + .050 [1.27]$$

FIG 3

-P: PICK & PLACE PAD
PLACE PPP-08 ON ϕ AS SHOWN

MATERIAL:
BODIES:
LIQUID CRYSTAL POLYMER
COLOR: BLACK
TERMINALS:
PHOSPHOR BRONZE

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:

REIDINGER 7-19-91

EXISPROD/ASSEMBLY/100
TSM5HSM

SHEET 02

PROPRIETARY NOTE:

THIS DOCUMENT IS THE PROPERTY OF SAMTEC CORPORATION. IT IS TO BE USED FOR THE PURPOSES SPECIFIED IN THE ORDER. IT IS NOT TO BE REPRODUCED, COPIED, OR DISTRIBUTED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF SAMTEC CORPORATION. SAMTEC CORPORATION IS NOT RESPONSIBLE FOR ANY DAMAGE TO PROPERTY OR PERSONS ARISING FROM THE USE OF THIS DOCUMENT.

FIG 1
-LC: LOCKING CLIP OPTION
CLIPS N/A WITH -A OPTION.