

PART NAME	POTTING BOX (STYLE A)	PART No.	PB-1560 TO PB-1565
-----------	-----------------------	----------	--------------------

MATERIAL: ABS THERMOPLASTIC (FLAMMABILITY RATING OF UL94-HB AT 0.055" THICKNESS)

SUGGESTED SERVICE TEMPERATURE: -20° TO +60° C.

COLOR: BLACK

FINISH: INSIDE SURFACES ARE TEXTURED FINISH.


COVER REDUCES
INSIDE HEIGHT BY DIM G (SEE TABLE)

ALL COVERS HAVE SMOOTH SURFACES.

LENGTH AND WIDTH DIMENSIONS ARE TAKEN FROM CLOSED END OF THE BOX. DIMENSIONS INCREASE SLIGHTLY AT OPEN END DUE TO TAPER.

ALL DIMENSIONS HAVE ±0.010 TOLERANCE UNLESS OTHERWISE SPECIFIED

SHIPPED IN PACKAGES OF 25.



PART No.	A	B	C	D	E	F	G		OPTIONAL COVER
PB-1560	.769	.769	.512	.032	.787	.787	.025		PBC-1560-C
PB-1561	1.948	.491	.591	.050	1.969	.512	.035		PBC-1561-C
PB-1562	.950	.950	.984	.040	.984	.984	.035		PBC-1562-C
PB-1563	1.546	1.546	.787	.037	1.573	1.573	.045		PBC-1563-C
PB-1564	1.750	1.159	.630	.050	1.772	1.181	.020		PBC-1564-C
PB-1565	2.708	1.914	1.378	.055	2.756	1.968	.060		PBC-1565-C

To learn more about plastic enclosures visit <http://www.budind.com/>