



Jet-Light ELH 38 IP 54 Strahler

Für den Außen- und Innenbereich.

- Ideal für den Einsatz bei Heimwerk- und Reparaturarbeiten, Camping oder Grillparty.
- Elektronisches Vorschaltgerät für hohe Energieeffizienz, flackerfreies Licht und geringe Erwärmung.
- Bruch- und schlagfestes Kunststoffgehäuse. Lampenabdeckung aus schlagfestem Polycarbonat.
- Mit ausklappbarem Standfuß.
- Sehr kompakte Bauform.
- Neopren-Gummianschlussleitung mit Schutzkontakt-Stecker.
- Inklusive 38 W Leuchtmittel.
- Im farbigen Verkaufs-Karton.
- Wirkungsgrad Vorschaltgerät: A3
- Energieeffizienzklasse: B

Jet-Light ELH 38 IP 54 spotlight

For use indoors and outdoors.

- Ideal for home improvement, repair work or camping.
- Electronic ballast for energy efficiency, flicker-free light and minimum heat output.
- Robust, break- and shock-resistant plastic housing. Cover made from break resistant polycarbonate.
- With foldable stand.
- Compact construction.
- With special rubber cable and water-jet protected earthed plug.
- 38 W bulb included.
- In colourful display-packaging.
- Ballast efficiency: A3
- Energy efficiency class: B



Artikel-Nr. Article No.	Barcode 4007123...	VPE UP	Kabellänge Cable length	Kabelbezeichnung Cable	Leistung Output	Lichtstrom Luminous flux	Wirkungsgrad Lampe Lamp efficacy	Farbtemperatur Colour temperature	Fassung Fittings
1 17270 0	592555	1	1,8 m	H05RN-F 3G1,0	38 W	2500 lm	66 lm/W	6400 K	GR10q

Empfohlenes Zubehör: / Recommended accessories:

Artikel-Nr. Article No.	Barcode 4007123...	VPE UP	Bezeichnung Description	Leistung Output	Lichtstrom Luminous flux	Wirkungsgrad Lampe Lamp efficacy	Farbtemperatur Colour temperature	Farbwiedergabeindex Colour rendering index	Fassung Fittings
1 17470 0	576265	1	Jet-Light-Leuchtmittel/bulb	38 W	2500 lm	66 lm/W	6400 K	80	GR10q